

Screw Cover Type 1 Pull Box

HOFFMAN ENCLOSURES INC



Designed for use as a junction box and pull box in commercial and general applications. Flush covers and door frames must be ordered separately for flush installations.

FEATURES

- Industry standard: NEMA/EEMAC Type 1
- Flat, removable covers fastened with plated steel screws
- Provision for grounding
- Mounting holes on back of box
- Unique keyhole screw slots in the cover permit removal of the cover without extracting the screws
- ANSI 61 gray polyester powder paint finish inside and out

Anixter No.	Vendor No.	Description
366304	ASE4X4X4	Pull box, 4 in. H x 4 in. W x 4 in. D
ASE6X6X4	ASE6X6X4	Pull box, 6 in. H x 6 in. W x 4 in. D
ASE8X8X4	ASE8X8X4	Pull box, 8 in. H x 8 in. W x 4 in. D
366307	ASE10X10X4	Pull box, 10 in. H x 10 in. W x 4 in. D
366308	ASE12X12X4	Pull box, 12 in. H x 12 in. W x 4 in. D
366309	ASE6X6X6	Pull box, 6 in. H x 6 in. W x 6 in. D
366310	ASE8X8X6	Pull box, 8 in. H x 8 in. W x 6 in. D
366311	ASE10X10X6	Pull box, 10 in. H x 10 in. W x 6 in. D
340344	ASE12X12X6	Pull box, 12 in. H x 12 in. W x 6 in. D
ASE18X18X6	ASE18X18X6	Pull box, 18 in. H x 18 in. W x 6 in. D
366314	ASE24X24X6	Pull box, 24 in. H x 24 in. W x 6 in. D
366315	ASE24X24X8	Pull box, 24 in. H x 24 in. W x 8 in. D

More sizes available and also without knockouts. For more information contact your sales representative.

Hinged Cover Type 1 Cutout Box

HOFFMAN ENCLOSURES INC



Designed for use as a surface-mounted junction box, service box, switch box or cutout box.

FEATURES

- Industry standard: NEMA/EEMAC Type 1
- 14- or 16-gauge steel
- Butt hinges
- Mounting holes on back of box
- Provision for grounding

4 IN. DEPTH

Anixter No.	Vendor No.	Description
366316	AHE6X6X4	6 in. H x 6 in. W
366317	AHE8X6X4	8 in. H x 6 in. W
366318	AHE8X8X4	8 in. H x 8 in. W
366319	AHE10X8X4	10 in. H x 8 in. W
366320	AHE10X10X4	10 in. H x 10 in. W
366321	AHE12X10X4	12 in. H x 10 in. W

6 IN. DEPTH

Anixter No.	Vendor No.	Description
366322	AHE10X8X6	10 in. H x 8 in. W
366323	AHE10X10X6	10 in. H x 10 in. W
366324	AHE12X12X6	12 in. H x 12 in. W
366325	AHE16X16X6	16 in. H x 16 in. W
355062	AHE18X18X6	18 in. H x 18 in. W
366326	AHE24X18X6	24 in. H x 18 in. W

More sizes available. For more information contact your sales representative.

## Rack, Console and Enclosure Solutions

## Hoffman

## Type 1 Enclosure

HOFFMAN ENCLOSURES INC



Designed for use in control and instrumentation applications in areas that do not require oil-tight and dust-tight specifications. Available perforated back panel reduces time required to mount components.

## FEATURES

- Industry standard: NEMA/EEMAC Type 1
- Flush slotted latch operated with a screwdriver. Optional latches available
- Weldnuts provided for mounting optional panels
- 16-gauge steel
- Butt hinges
- Mounting holes on back of enclosure
- ANSI 61 gray polyester powder paint finish inside and out

## ENCLOSURES

Anixter No.	Vendor No.	Description
366327	A6N64	Type 1 small enclosure, 6 in. H x 6 in. W x 4 in. D
366328	A8N64	Type 1 small enclosure, 8 in. H x 6 in. W x 4 in. D
366329	A8N84	Type 1 small enclosure, 8 in. H x 8 in. W x 4 in. D
366330	A12N104	Type 1 small enclosure, 12 in. H x 10 in. W x 4 in. D
366331	A12N124	Type 1 small enclosure, 12 in. H x 12 in. W x 4 in. D
366332	A8N86	Type 1 small enclosure, 8 in. H x 8 in. W x 6 in. D
366333	A10N106	Type 1 small enclosure, 10 in. H x 10 in. W x 6 in. D
366334	A12N126	Type 1 small enclosure, 12 in. H x 12 in. W x 6 in. D
366335	A14N126	Type 1 small enclosure, 14 in. H x 12 in. W x 6 in. D
366336	A16N126	Type 1 small enclosure, 16 in. H x 12 in. W x 6 in. D
366337	A20N16ALP	Type 1 medium enclosure, 20 in. H x 16 in. W x 6.62 in. D
366338	A20N20ALP	Type 1 medium enclosure, 20 in. H x 20 in. W x 6.62 in. D
255674	A24N24ALP	Type 1 medium enclosure, 24 in. H x 24 in. W x 6.62 in. D
366339	A20N12BLP	Type 1 medium enclosure, 20 in. H x 12 in. W x 8.62 in. D

Anixter No.	Vendor No.	Description
366340	A20N20BLP	Type 1 medium enclosure, 20 in. H x 20 in. W x 8.62 in. D
366341	A24N20BLP	Type 1 medium enclosure, 24 in. H x 20 in. W x 8.62 in. D
366342	A24N24BLP	Type 1 medium enclosure, 24 in. H x 24 in. W x 8.62 in. D
366343	A24N24DLP	Type 1 medium enclosure, 24 in. H x 24 in. W x 12.62 in. D
A42N3609	A42N3609	Type 1 large enclosure, 42 in. H x 36 in. W x 9.25 in. D

## ACCESSORIES

Anixter No.	Vendor No.	Description
366344	A6N6PP	Perforated back panel for 6 in. H x 6 in. W small enclosure
366345	A8N6PP	Perforated back panel for 8 in. H x 6 in. W small enclosure
366346	A8N8PP	Perforated back panel for 8 in. H x 8 in. W small enclosure
335283	A10N10PP	Perforated back panel for 10 in. H x 10 in. W small enclosure
366347	A12N10PP	Perforated back panel for 12 in. H x 10 in. W small enclosure
366348	A12N12PP	Perforated back panel for 12 in. H x 12 in. W small enclosure
366349	A14N12PP	Perforated back panel for 14 in. H x 12 in. W small enclosure
366350	A16N12PP	Perforated back panel for 16 in. H x 12 in. W small enclosure
366351	A16N12MPP	Perforated back panel for 16 in. H x 12 in. W medium enclosure
366352	A20N12MPP	Perforated back panel for 20 in. H x 12 in. W medium enclosure
366353	A20N16MPP	Perforated back panel for 20 in. H x 16 in. W medium enclosure
366354	A20N20MPP	Perforated back panel for 20 in. H x 20 in. W medium enclosure
366355	A24N20MPP	Perforated back panel for 24 in. H x 20 in. W medium enclosure
331032	A24N24MPP	Perforated back panel for 24 in. H x 24 in. W medium enclosure
A42P36	A42P36	Solid back panel for 42 in. H x 36 in. W large enclosure
AL12AR	AL12AR	Optional cylinder lock kit

More sizes available. For more information contact your sales representative.

**Type 1 Control Box**

HOFFMAN ENCLOSURES INC



This convenient combination enclosure, with a perforated-panel assembly, provides a ready solution for mounting electrical control gear. The enclosed panel is perforated to reduce the time required to mount components. Use a #8 self-tapping screw to attach components directly onto the panel, eliminating the need to measure, mark and drill.

**FEATURES**

- Industry standard: NEMA/EEMAC Type 1
- Door has key lock quarter-turn latch; two keys included
- Includes removable 16-gauge gray perforated panel
- ANSI 61 gray polyester powder paint finish inside and out

Anixter No.	Vendor No.	Description
A12126T1PP	A12126T1PP	Type 1 enclosure with lock and panel, 12 in. H x 12 in. W x 6 in. D
A16126T1PP	A16126T1PP	Type 1 enclosure with lock and panel, 16 in. H x 12 in. W x 6 in. D
A2016AT1PP	A2016AT1PP	Type 1 enclosure with lock and panel, 20 in. H x 16 in. W x 6.62 in. D
A2420AT1PP	A2420AT1PP	Type 1 enclosure with lock and panel, 24 in. H x 20 in. W x 6.62 in. D
A3624AT1PP	A3624AT1PP	Type 1 enclosure with lock and panel, 36 in. H x 24 in. W x 6.62 in. D
A3630AT1PP	A3630AT1PP	Type 1 enclosure with lock and panel, 36 in. H x 30 in. W x 6.62 in. D

**Type 3R Enclosures**

HOFFMAN ENCLOSURES INC

Designed for use as a wiring box and junction box. Enclosure provides protection against rain, sleet and snow in outdoor installations or against dripping water in indoor installations.

**FEATURES**

- Industry standard: NEMA/EEMAC Type 3R
- Drip-shield top and seam-free sides, front and back
- Slip-on removable cover fastened with plated steel screws along the bottom edge
- Provision for padlocking
- No gasketing
- ANSI 61 gray polyester powder paint finish inside and out

**SCREW COVER**



Anixter No.	Vendor No.	Description
366672	A4R44	4 in. H x 4 in. W x 4 in. D
366673	A6R64	6 in. H x 6 in. W x 4 in. D
259511	A8R64	8 in. H x 6 in. W x 4 in. D
259513	A8R84	8 in. H x 8 in. W x 4 in. D
366674	A10R104	10 in. H x 10 in. W x 4 in. D
316679	A12R124	12 in. H x 12 in. W x 4 in. D
366675	A6R66	6 in. H x 6 in. W x 6 in. D
366676	A8R86	8 in. H x 8 in. W x 6 in. D
366677	A10R106	10 in. H x 10 in. W x 6 in. D
366678	A12R126	12 in. H x 12 in. W x 6 in. D
366679	A16R126	16 in. H x 12 in. W x 6 in. D
366680	A18R186	18 in. H x 18 in. W x 6 in. D
366681	A24R246	24 in. H x 24 in. W x 6 in. D
366682	A12R128	12 in. H x 12 in. W x 8 in. D
366683	A18R188	18 in. H x 18 in. W x 8 in. D
366684	A24R248	24 in. H x 24 in. W x 8 in. D

**HINGED COVER**



Anixter No.	Vendor No.	Description
366685	A6R44HCR	6 in. H x 4 in. W x 4 in. D
317368	A6R64HCR	6 in. H x 6 in. W x 4 in. D
366686	A8R64HCR	8 in. H x 6 in. W x 4 in. D
366687	A8R86HCR	8 in. H x 8 in. W x 6 in. D
366688	A10R86HCR	10 in. H x 8 in. W x 6 in. D
366689	A12R106HCR	12 in. H x 10 in. W x 6 in. D
366690	A12R126HCR	12 in. H x 12 in. W x 6 in. D
366691	A12R1210HCR	12 in. H x 12 in. W x 10 in. D

## Rack, Console and Enclosure Solutions

# Hoffman

### Type 3R Telephone Cabinet

HOFFMAN ENCLOSURES INC

Designed as a wall-mount telephone-termination cabinet that is suited for outdoor and indoor use. These cabinets are also used for mounting and protecting telecommunications circuit accessories, cross-connect terminal block assemblies, maintenance-terminal modules, cable-splice enclosures, network-interface devices, wire-guide assemblies and telephone protectors.

#### FEATURES

- Industry standard: NEMA Type 3R
- Lift-off hinges
- Four-position grounding bar #14-2/0
- Tamper-resistant quarter-turn latch, 7 mm square drive; opens with 5/16 12-point socket
- Padlock hasp
- 3/4 in.-thick plywood panel
- ANSI 61 gray polyester powder paint finish inside and out

SINGLE-DOOR



Anixter No.	Vendor No.	Description
366692	ATC26R248	26 in. H x 24 in. W x 8 in. D
366693	ATC36R248	36 in. H x 24 in. W x 8 in. D
366694	ATC36R369	36 in. H x 36 in. W x 9 in. D
366697	ATC36R3612	36 in. H x 36 in. W x 12 in. D
366698	ALTC3R	Locking T-handle accessory

DOUBLE-DOOR



Anixter No.	Vendor No.	Description
366695	ATC48R369	48 in. H x 36 in. W x 9 in. D
366696	ATC48R489	48 in. H x 48 in. W x 9 in. D
366698	ALTC3R	Locking T-handle accessory

More sizes available. For more information contact your sales representative.

### Type 4x Fiberglass Hinged Cover Wi-Fi Cabinet

HOFFMAN ENCLOSURES INC



Provides a secure enclosure for wireless equipment in both indoor and outdoor locations. Ideal for locations such as tunnels, floor vaults, marinas, outside walls and rooftops. Fiberglass construction allows Wi-Fi and WLAN signals to pass through the cabinet unimpeded. Lightweight for easy mounting. Solid covers are shown below; window covers are also available. Covers are secured with screws; optional quick-release latches are available.

#### FEATURES

- Industry standard: NEMA/EEMAC Type 4X
- Enclosures and cover made of molded fiberglass polyester that resists chemicals and temperature change
- Includes a 3/4 in. plywood panel for mounting equipment
- Seamless foam-in-place gasket assures watertight and dust-tight seal
- Screw cover enclosures are secured with two captivated Type 316 stainless steel slotted cross point cover screws

Anixter No.	Vendor No.	Description
366699	D664CHSCFGP	6 in. H x 6 in. W x 4 in. D
317883	D16148CHSCFGP	16 in. H x 14 in. W x 8 in. D
366700	D181610CHSCFGP	18 in. H x 16 in. W x 10 in. D

Also available with window cover. For more information contact your local sales representative.

### ACCESSPLUS II Type 1 Double-hinged Wall-mount Cabinets

HOFFMAN ENCLOSURES INC



ACCESSPLUS II Cabinets provide security, equipment access, cooling and support for network and other 19 in. rack-mount equipment. The cabinet has three components: front door, center section and wall section. Double-hinged for easy equipment access; center section provides 19 in. rack mounting per EIA universal spacing and is accessed through the front door or swing the center section away from the wall section for rear access.

#### FEATURES

- Industry standard: NEMA Type 1
- Front door has either a solid steel or hardened, tinted safety-glass window door for superior scratch resistance

- Center section easily removed from rear section; tool-less one-person installation possible
- Self-locking center-to-wall section latches in two locations
- Front access to all latches (no exposed side latches); cabinet can be installed tightly in corners
- Vented sides provide cross-flow ventilation to improve heat dissipation
- RAL 9005 black light-textured, low-gloss polyester powder paint

ACCESSPLUS II CABINETS WITH WINDOW DOOR

Anixter No.	Vendor No.	Description
394585	EWMW242418	24 in. H x 24 in. W x 18 in. D, 12RU
394586	EWMW362418	36 in. H x 24 in. W x 18 in. D, 19RU
394587	EWMW482418	48 in. H x 24 in. W x 18 in. D, 26RU
390048	EWMW242425	24 in. H x 24 in. W x 25 in. D, 12RU
390051	EWMW362425	36 in. H x 24 in. W x 25 in. D, 19RU
390053	EWMW482425	48 in. H x 24 in. W x 25 in. D, 26RU

ACCESSPLUS II CABINETS WITH SOLID DOOR

Anixter No.	Vendor No.	Description
394588	EWMS242418	24 in. H x 24 in. W x 18 in. D, 12RU
394589	EWMS362418	36 in. H x 24 in. W x 18 in. D, 19RU
394590	EWMS482418	48 in. H x 24 in. W x 18 in. D, 26RU
394591	EWMS242425	24 in. H x 24 in. W x 25 in. D, 12RU
394592	EWMS362425	36 in. H x 24 in. W x 25 in. D, 19RU
394593	EWMS482425	48 in. H x 24 in. W x 25 in. D, 26RU

ADDITIONS

Anixter No.	Vendor No.	Description
406107	EWMF1	Fan kit, fits 18 in. deep cabinets
403920	EWMF2	Fan kit, fits 25 in. and 30 in. deep cabinets

More sizes and configurations available. For more information contact your sales representative.

PROTEK DH Type 4 and Type 12 Double-hinged Wall-mount Cabinet

HOFFMAN ENCLOSURES INC



This Hoffman double-hinged wall-mounted cabinet is ideal for protecting 19 in. network equipment from falling dirt, splashing water, dust and other contaminants. This versatile cabinet mounts to a wall or can be pole-mounted with the optional pole-mounting kit. Designed to hold multiple pieces of voice/data equipment comfortably, it can be mounted to be left- or right-hinged and comes completely assembled and ready to mount.

FEATURES

- Industry standard: NEMA/EEMAC Type 4 or 12
- Also available in UL Type 4X stainless steel
- Solid door provides complete physical and visual protection
- Window door, made with scratch-resistant safety glass, allows equipment monitoring without opening the door
- Double-hinged for easy equipment access
- Foam-in-place seamless gasket around door seals against outdoor air infiltration and is nonabsorbing and chemical resistant
- Type 12 cabinets have solid or window doors and a locking wing knob with two keys. They provide security and convenience in indoor applications
- Type 4 cabinets have solid doors and a padlock capable 1/4-turn latch. They provide easy operation and locking options in indoor and outdoor applications
- One set of adjustable tapped 19 in. rack angles included
- RAL 7035 light gray textured, low-gloss polyester powder paint

PROTEK DH WALL-MOUNT CABINETS



Anixter No.	Vendor No.	Description
460228	PTHW162415G2	Type 12, window door, 16 in. H x 24 in. W x 15 in. D, 7RU
460229	PTHW242415G2	Type 12, window door, 24 in. H x 24 in. W x 15 in. D, 12RU
460230	PTHW242424G2	Type 12, window door, 24 in. H x 24 in. W x 24 in. D, 12RU
460232	PTHW362415G2	Type 12, window door, 36 in. H x 24 in. W x 15 in. D, 19RU
460233	PTHW362424G2	Type 12, window door, 36 in. H x 24 in. W x 24 in. D, 19RU
460236	PTHW482415G2	Type 12, window door, 48 in. H x 24 in. W x 15 in. D, 26RU
460247	PTHW482424G2	Type 12, window door, 48 in. H x 24 in. W x 24 in. D, 26RU
460222	PTHS242424G4	Type 4 and 12, solid door, 24 in. H x 24 in. W x 24 in. D, 12RU
460224	PTHS362424G4	Type 4 and 12, solid door, 36 in. H x 24 in. W x 24 in. D, 19RU
460226	PTHS482424G4	Type 4 and 12, solid door, 48 in. H x 24 in. W x 24 in. D, 26RU

Continued on next page >>

## Rack, Console and Enclosure Solutions

## Hoffman

(continued) PROTEK DH Type 4 and Type 12 Double-hinged Wall-mount Cabinet

## PROTEK DH FAN PACKAGE

PROTEK DH Fan packages provide an integral solar top/drip shield and thermostatically controlled fans to provide airflow to cool internal equipment. Available in UL Type 3R for outdoor use.

Anixter No.	Vendor No.	Description
488288	PTHS242424G3	Type 3R, solid door, 24 in. H x 24 in. W x 24 in. D, 12RU
480607	PTHS362424G3	Type 3R, solid door, 36 in. H x 24 in. W x 24 in. D, 19RU
492586	PTHS482424G3	Type 3R, solid door, 48 in. H x 24 in. W x 24 in. D, 26RU

More sizes and configurations available. For more information contact your sales representative.

## DVR and 19 in. Rack Equipment Cabinet

HOFFMAN ENCLOSURES INC



These cabinets provide physical protection and access control to DVR, 19 in. equipment or other equipment. Mount the cabinet vertically or horizontally.

## FEATURES

- Industry standard: NEMA Type 1
- Top cover has tool-less removal, is captivated by door and secured by keylock, providing easy access and installation
- Solid front door has 180 degree opening continuous hinge
- Vented sides dissipate heat from equipment
- A fan-ready cutout is provided
- 19 in. rack angles and hardware included
- Doors and body made of 18-gauge steel; top cover is 16-gauge steel
- RAL 9005 black, light-textured, low-gloss polyester powder paint

Anixter No.	Vendor No.	Description
394599	DVR4U	4RU cabinet, 9.5 in. H x 21.7 in. W x 18.4 in. D
394604	DVR6U	6RU cabinet, 13 in. H x 21.7 in. W x 18.4 in. D
394598	A4AXFNPGQ	4 in. fan, 115 V AC, with plug

# **NEW** Middle Atlantic Monitor Walls



*From Concept*



*to Reality*

## **In Only Three Weeks**

*It just doesn't get any easier than this!*

Use our **free** Middle Atlantic Designer<sup>®</sup> software to describe the ideal monitor wall arrangement, up to 13' high and unlimited width. If you know the size and arrangement of the monitors, you can finish in less than two minutes, and send us the file.

We'll get back to you with a design and timing confirmation, and once confirmed, your new video wall can be on the way to installation in three weeks or less.

### **Let us show you!**

Contact your Middle Atlantic Representative  
or our technical support team at: 800-266-7225

*This new system includes  
Installation-friendly features  
such as hidden cable  
routing channels.*

**Middle Atlantic Products**  
EXCEPTIONAL SUPPORT & PROTECTION™  
[www.middleatlantic.com](http://www.middleatlantic.com)

## Rack, Console and Enclosure Solutions

# Middle Atlantic

### ViewPoint Technical Furniture

MIDDLE ATLANTIC PRODUCTS



Serious furniture for mission-critical installations.

#### FEATURES

- Modular design allows economical additions and limitless configuration choices
- Consoles are optimized for flexible flat-screen arrangements and ergonomically designed with the user in mind
- Fully welded bays provide a heavy-duty structure that can be assembled quickly
- Available with an 18 in. deep work surface or 34 in. desktop
- UL Listed in the U.S. and Canada
- GREENGUARD IAQ-certified
- LCD monitors can be mounted using optional monitor arms
- Ergonomically designed professional-use operator chair available

A variety of finishes are available. Contact your sales representative. Middle Atlantic has free layout software for console designs.

### VisionFrame Video Monitor Wall

MIDDLE ATLANTIC PRODUCTS



Robust video monitor support system application engineered for unparalleled monitor support.

#### FEATURES

- Assembles quickly and easily
- Integral cable management channels
- Accepts 10 in. to 80 in. monitors
- Walls can be designed up to 13 ft. 3 in. high, in any width
- Free-standing and desk-mount models available
- Power strips mount directly to the frame
- ETL Listed in the U.S. and Canada for strength and stability

Also available as desk wall version that attaches directly to the Middle Atlantic ViewPoint console and LCD desk line. Call your local sales representative.

### LCD Monitoring Desk System

MIDDLE ATLANTIC PRODUCTS



Versatile, configurable monitoring desk system provides more useable space in a smaller footprint and is optimized for use with LCD screens. Satisfying the need for optimized technical furniture, the highly modular LCD Monitoring Desk System is equally suited for single-desk surveillance applications or larger-scale command-and-control environments.

For additional LCD Monitoring Consoles or accessories, please contact your sales representative.

Anixter No.	Vendor No.	Description
275169	LD-L48	Light bridge for 48 in. desk
275170	LD-L64	Light bridge for 64 in. desk
275220	LD-M2X1	Monitor mount, 2 monitors, 2 across
275222	LD-M2X2	Monitor mount, 4 monitors, 2 across, 2 levels
275221	LD-M3X1	Monitor mount, 3 monitors, 3 across
275225	D-PT20	Pencil tray, 20 in. wide, mounts under desk
369796	LD-4830	48 in. wide LCD desk, specify color*
369799	LD-6430	64 in. wide LCD desk, specify color*
369802	LD-SP30	Pair of half-height side panels for LCD desks, specify color*
369807	LD-PSP30	Pair of full-height side panels for LCD desks, specify color*
369901	LD-M3X2	Monitor mount, 6 monitors 3 across, 2 levels

\* Add -DC for Dark Cherry, -HM for Honey Maple, -PS for Pepperstone or -SL for Slate (available for side panels only) at the end of the vendor number for color.

### Quiet-Cool and Convective Series Monitoring Consoles

MIDDLE ATLANTIC PRODUCTS



The modular design of Quiet-Cool Series and Convective Series consoles allows for limitless configurations. The combinations of base modules, top tiers, corner wedges



and writing surface option allow designs that can match any requirements, and assemble in a third of the time of knock-down consoles.

Console configuration can be ordered quickly and easily with a single part number. When passive cooling is needed, select Convective Series configurations, and choose the Quiet-Cool Series for systems requiring active cooling. Each configuration includes the same features and benefits that are an integral part of Middle Atlantic's consoles.

## FEATURES

- Welded design ships fully assembled to minimize installation time
- 14-gauge construction provides a robust 1,500 lb. weight capacity
- Space saving 22 in. W, 27 in. D.
- Optional sliding rotating rack bay available
- Convective Series Consoles are Seismic Certified (UBC and CBC Zone 4 and IBC, ASCE, and FPA Seismic use Group III) for protecting 375 lb. of equipment when used with SC-Z4 brackets
- Granite gray color standard; black and light gray also available standard
- UL Listed in the U.S. and Canada
- Each configuration comes complete with:
  - Locking solid front door on each bay
  - 25 rack screws per bay
  - Ganging hardware
  - 15-amp power distribution

### CONVECTIVE SERIES

Anixter No.	Vendor No.	Description
369772	SC-2	2-bay straight convective console configuration package
369775	SC-3	3-bay straight convective console package
369781	SC-3W2	3-bay convective console configuration package with wedges
369777	SC-4	4-bay straight convective console package
369785	SC-4W2	4-bay convective console configuration package with wedges
369791	SC-5W2-53T	5-bay convective console configuration package with wedges and third tiers

### QUIET-COOLING SERIES

Anixter No.	Vendor No.	Description
369774	SCQ-2	2-bay straight Quiet-Cool console configuration package
369776	SCQ-3	3-bay straight Quiet-Cool console configuration package
369783	SCQ-3W2	3-bay Quiet-Cool console configuration package with wedges
327166	SCQ-4	4-bay straight Quiet-Cool console configuration package
369789	SCQ-4W2	4-bay Quiet-Cool console configuration package with wedges
369793	SCQ-5W2-53T	5-bay Quiet-Cool console configuration package with wedges and third tiers

## Pivoting Panel Mount

MIDDLE ATLANTIC PRODUCTS



Wall-mount racks provide easy rear access.

## FEATURES

- Unique design allows punching down while fully open
- Available in three depths: 6 in., 12 in. and 18 in.
- Abundant internal tie points for cable management
- Includes Velcro cable loops

Anixter No.	Vendor No.	Description
240825	PPM-2	3 1/2 in. (2-rack space)
231155	PPM-4	7 in. (4-rack space)
231159	PPM-6	10 1/2 in. (6-rack space)
231167	PPM-6-12	10 1/2 in. (6-rack space), 12 in. deep
231168	PPM-8-12	14 in. (8-rack space), 12 in. deep
231169	PPM-8-18	14 in. (8-rack space), 18 in. deep

## WRS Series 19-in. Low-profile Wall-mount Rack

MIDDLE ATLANTIC PRODUCTS



The WRP/WRS Series low-profile wall cabinets allow mounting of equipment in a vertical "knobs-up" fashion for space efficiency and aesthetics.

## FEATURES

- Adjustable rackrail providing 20 in. to 23 in. of useable racking depth
- Has a vented bottom, two bottom-located fan-mounting positions with grills (fans not included)
- The angled top cover with hinged plexiglass for the WRP and solid steel for the WRS allows convenient equipment access
- Keyed separately from the body keylock to provide user access to front-equipment controls while limiting access to connections in the rear of the equipment
- Available in black or putty colors
- UL Listed in the U.S. and Canada

Continued on next page >>

## Rack, Console and Enclosure Solutions

# Middle Atlantic

### (continued) WRS Series 19-in. Low-profile Wall-mount Rack

#### WITH SOLID STEEL TOP COVER

23 in. deep, black color

Anixter No.	Vendor No.	Description
275132	WRS-4	7 in. racking height (4 space)
231269	WRS-6	10 1/2 in. racking height (6 space)
231272	WRS-8	14 in. racking height (8 space)

#### WITH PLEXIGLASS TOP COVER

23 in. deep, putty color

Anixter No.	Vendor No.	Description
231266	WRP-4	7 in. racking height (4 space)
231265	WRP-6	10 1/2 in. racking height (6 space)
268474	WRP-8	14 in. racking height (8 space)

### Adjustable-depth Hinged Panel-mount Rack

MIDDLE ATLANTIC PRODUCTS



Economical hinged wall mount provides easy rear access to rack-mount components.

#### FEATURES

- One side hinged at two points for easy rear access
- Built-in cable management
- Includes four 10-32 rack screws
- Grounding stud built in
- Space indicators marked on rackrail
- Adjustable depth - 9 in. to 15 in.

Anixter No.	Vendor No.	Description
421695	HPM-4-915	4-rack space
421696	HPM-6-915	6-rack space
421693	HPM-8-915	8-rack space

### Vertical Panel Wall Mount

MIDDLE ATLANTIC PRODUCTS



Cost-effective, versatile solution to wall-mount racking.

#### FEATURES

- Can accommodate all depths of equipment
- Mounts horizontally or vertically allowing versatile component placement
- Heavy-duty threaded rackrail

Anixter No.	Vendor No.	Description
421697	VPM-2	2-rack space
421698	VPM-3	3-rack space
421699	VPM-4	4-rack space

### DWR Series Sectional Wall Racks

MIDDLE ATLANTIC PRODUCTS



Specify a DWR wall cabinet when floor space is an issue. This pivoting, sectional wall cabinet is ideal for larger systems in both secure and non-secure areas. Equipped with fully-adjustable 11-gauge, 10-32 threaded rackrail and advanced cable-management systems, Middle Atlantic's DWR series welded sectional wall racks feature 16-gauge steel construction and are offered in depths of 17 in., 22 in., 26 in. and 32 in.

#### FEATURES

- Sectional wall rack
- Finished in durable black powder coat
- New Tool-Free Quick-Mount system for easy, one-person mounting of the center section to the backpan on the job site
- Up to 300 lb. capacity depending on model
- Superior natural ventilation with additional cooling available with optional fans
- Abundant built-in cable lacing points in interior
- UL Listed in the U.S. and Canada
- Accepts the new Zero Clearance Latch which allows mounting side-by-side or in a corner
- Available in granite gray

#### 17 IN. DEPTH (15 IN. USEABLE)

Anixter No.	Vendor No.	Description
240830	DWR-35-17	68 5/16 in. high, 35-rack space, 300 lb. weight capacity
240827	DWR-24-17	49 1/16 in. high, 24-rack space, 300 lb. weight capacity
275120	DWR-24-17PD	49 1/16 in. high, 24-rack space, 300 lb. weight capacity, includes plexiglass door
240828	DWR-21-17	43 3/16 in. high, 21-rack space, 250 lb. weight capacity
275121	DWR-21-17PD	43 13/16 in. high, 21-rack space, 250 lb. weight capacity, includes plexiglass door
240829	DWR-18-17	38 9/16 in. high, 18-rack space, 250 lb. weight capacity

## Middle Atlantic

Anixter No.	Vendor No.	Description
240835	DWR-16-17	35 1/16 in. high, 16-rack space, 200 lb. weight capacity
275122	DWR-16-17PD	35 1/16 in. high, 16-rack space, 200 lb. weight capacity, includes plexiglass door
240836	DWR-12-17	28 1/16 in. high, 12-rack space, 200 lb. weight capacity
231165	DWR-10-17	17 1/2 in. high, 10-rack space, 200 lb. weight capacity
268467	DWR-10-17PD	17 1/2 in. high, 10-rack space, 200 lb. weight capacity, includes plexiglass door

## 22 IN. DEPTH (20 IN. USEABLE)

Anixter No.	Vendor No.	Description
240831	DWR-35-22	68 5/16 in. high, 35-rack space, 300 lb. weight capacity
275123	DWR-35-22PD	68 5/16 in. high, 35-rack space, 300 lb. weight capacity, includes plexiglass door
231177	DWR-24-22	49 1/16 in. high, 24-rack space, 300 lb. weight capacity
247021	DWR-24-22PD	49 1/16 in., 24-rack space, 300 lb. weight capacity, includes plexiglass door
240832	DWR-21-22	43 3/16 in. high, 21-rack space, 250 lb. weight capacity
229932	DWR-21-22PD	43 13/16 in. high, 21-rack space, 250 lb. weight capacity, includes plexiglass door
231173	DWR-18-22	38 9/16 in. high, 18-rack space, 200 lb. weight capacity
240833	DWR-16-22	35 1/16 in. high, 16-rack space, 200 lb. weight capacity
268471	DWR-16-22PD	22 in. deep, 16-rack space, DWR with plexiglass front door, 200 lb. weight capacity
240834	DWR-12-22	28 1/16 in. high, 12-rack space, 200 lb. weight capacity
231170	DWR-10-22	17 1/2 in. high, 10-rack space, 200 lb. weight capacity
264574	DWR-10-22-PD	24 9/16 in. high, 10-rack space, 200 lb. weight capacity, includes plexiglass door

## 26 IN. DEPTH (24 IN. USEABLE)

Anixter No.	Vendor No.	Description
275124	DWR-35-26	68 5/16 in. high, 35 rack space, 300 lb. weight capacity
275125	DWR-35-26PD	68 5/16 in. high, 35 rack space, 300 lb. weight capacity, includes plexiglass door
275126	DWR-24-26	49 1/16 in. high, 24-rack space, 300 lb. weight capacity
275127	DWR-24-26PD	49 1/16 in., 24-rack space, 300 lb. weight capacity, includes plexiglass door
275128	DWR-18-26	38 9/16 in. high, 18-rack space, 250 lb. weight capacity
275129	DWR-18-26PD	38 9/16 in. high, 18 rack space, 250 lb. weight capacity, includes plexiglass door

Anixter No.	Vendor No.	Description
275130	DWR-12-26	28 1/16 in. high, 12-rack space, 200 lb. weight capacity
275131	DWR-12-26PD	28 1/6 in. high, 12-rack space, 200 lb. weight capacity, DWR with plexiglass front door

## 32 IN. DEPTH (30 IN. USEABLE)

Anixter No.	Vendor No.	Description
371053	DWR-24-32	49 1/16 in. high, 24-rack space, 300 lb. weight capacity
371052	DWR-1832	38 9/16 in. high, 18-rack space, 250 lb. weight capacity
371051	DWR-12-32	28 1/16 in. high, 12-rack space, 200 lb. weight capacity

## Swing-frame Wall Rack

MIDDLE ATLANTIC PRODUCTS



Open wall-mount racks.

## FEATURES

- Open-back design maximizes usable wall space
- 90-degree opening with positive stop facilitates punching down of wires
- Ships ready-to-assemble to reduce space needed for storage and transport
- Unique, open-swing frame design utilizes pivot points instead of hinges and can be inverted to allow opening from the left or the right
- Durable black powder-coat finish
- 50 rack screws included
- Abundant tie points and cable pass-throughs ease cable management
- Permanently lubricated bushings with a proprietary pivot prevent sag

## 18 IN. DEEP RACKS

Anixter No.	Vendor No.	Description
259902	SFR-12-18	12-rack space
259904	SFR-20-18	20-rack space
375077	SFR-25-18	25-rack space

## 24 IN. DEEP RACKS

Anixter No.	Vendor No.	Description
421701	SFR-12-24	12-rack space
421702	SFR-20-24	20-rack space
421703	SFR-25-24	25-rack space

## Rack, Console and Enclosure Solutions

# Middle Atlantic

### SBX Series 19 in. Wall-mount Rack

MIDDLE ATLANTIC PRODUCTS



The SBX series enclosures offer an economical solution to those seeking a wall-mount rack for smaller systems. The fully welded construction utilizes 18-gauge steel, incorporates a locking front door which swings open a full 180 degrees on a virtually indestructible hinge, and includes a removable backpan for easier wall mounting. Ventilation slots at the top of each side provide superior cooling, while a deep rail-to-door clearance ratio provides flexibility not found in flush-mount door designs. Additional features include 11-gauge threaded 10-32 rackrails, 1/2 in. and 3/4 in. electrical knockouts at top, bottom and rear and a black textured powder-coat finish.

Anixter No.	Vendor No.	Description
231289	SBX-7	12 1/4 in. high, 7-rack space, 14 in. deep, 75 lb. capacity
240784	SBX-10	17 1/2 in. high, 10-rack space, 14 in. deep, 100 lb. capacity

### SR 19 in. Pivoting Rack

MIDDLE ATLANTIC PRODUCTS



Wall rack pivots on a floor base for easy equipment access.

#### FEATURES

- Fully welded construction, 16-gauge steel
- UL Listed in the U.S. and Canada
- 500 lb. weight capacity
- Backpan features a large laser knock-out panel and accommodates 89-D brackets and electrical boxes when used with optional subplate. Backpan accepts up to four subplates
- Bottom cable-entry platform supports entire weight of rack on floor
- 70 in. (40-space)
- One subplate mounting kit for 89-D type brackets and electrical boxes, includes mounting hardware

#### SWING-OUT CABINET DESIGN

Floor and wall supported

Anixter No.	Vendor No.	Description
319793	SR-24-28	Swing-out cabinet, floor and wall-supported, 24 RMU, 28 in. D
319794	SR-24-32	Swing-out cabinet, floor and wall-supported, 24 RMU, 32 in. D
231228	SR-40-22	Swing-out cabinet, floor and wall-supported, 40 RMU, 22 in. D
255593	SR-40-28	Swing-out cabinet, floor and wall-supported, 40 RMU, 28 in. D
305194	SR-40-32	Swing-out cabinet, floor and wall-supported, 40 RMU, 32 in. D
305454	SR-46-28	Swing-out cabinet, floor and wall-supported, 46 RMU, 28 in. D

#### ACCESSORIES

Anixter No.	Vendor No.	Description
231140	PFD-24	Plexiglass front door, 24 RMU
231151	PFD-40	Plexiglass front door, 40 RMU
255016	FD-24	Solid front door, 24 RMU
255015	FD-40	Solid front door, 40 RMU
231251	VFD-24	Vented front door, 24 RMU
231254	VFD-40	Vented front door, 40 RMU
240824	SR-SUB	Subplate mounting kit
302340	DWR-RR24	Additional rackrail, 24 RMU
275138	DWR-RR40	*Additional rackrail, 40 RMU
369836	DWR-RR46	Additional rackrail, 46 RMU

\*Fits both SR-40-28 and SR-40-22

### MK Cable Management Racks

MIDDLE ATLANTIC PRODUCTS



Engineered for high-density patching applications.

#### FEATURES

- Two mounting depths available: 16 7/16 in. (6 3/8 in. usable) and new 24 in. (14 in. usable)
- Oversized cable ducts manage massive cable bundles
- Seismic-certified to the UBC 1997 and 2001 CBC Seismic Zone 4 and the IBC 2000, IBC 2003, 2002 ASCE Standard 7 and 2003 NFPA 5000 Seismic Use Group III for protecting 500 lb. of essential equipment in upper-floor installations with an Ip value of 1.5
- Unique swiveling front D-Rings provide patch-cable management
- Integral top-cable tray, front and rear
- Modern design incorporates captive fasteners

# Middle Atlantic

- Hook-and-loop fasteners and front cable feed-thru holes included
- 100 rack screws included

Anixter No.	Vendor No.	Description
231191	MK-19-45	Overall height 84 1/4 in., 16 7/16 in. depth
337232	MK-1945-24	Overall height 84 1/4 in., 24 in. depth

## VMRK-54 19 in. 54-space Rack Enclosure

MIDDLE ATLANTIC PRODUCTS



54-space enclosure provides more racking height.

### FEATURES

- 100 5/8 in. O.D. height, 54 useable spaces
- 31 in. O.D. depth
- UL Listed in the U.S. and Canada
- Broadcast standard 22 in. width
- Fully welded construction
- Substantial 2,500 lb. weight capacity
- Two pairs threaded 10-32 "Z-RAIL" standard
- Seismic Certified (UBC and CBC Zone 4 and IBC, ASCE, and NFPA Seismic use Group III) for protecting 600 lb. of equipment when used with MRK-Z4 bracket

Anixter No.	Vendor No.	Description
240837	VMRK-54	54 RMU VMRK cabinet frame, 31 in. deep with rear door
254081	MRK-Z4	Seismic bracket for MRK and VMRK cabinets

## MRK Series 19 in. Gangable Enclosures

MIDDLE ATLANTIC PRODUCTS



These racks feature a narrow design for large-scale multibay jobs, and accept optional removable side panels for easy equipment access.

### FEATURES

- Fully welded construction, open sides
- UL Listed in the U.S. and Canada
- Substantial 2,500 lb. weight capacity
- Slim 22 in. O.D. width

- Available with ProLiant style cage-nut rackrail
- Seismic Certified (UBC and CBC Zone 4 and IBC, ASCE, and NFPA Seismic use Group III) for protecting 1,000 lb. of equipment when used with MRK-Z4 brackets

### 26 1/2 IN. OUTSIDE DEPTH

Anixter No.	Vendor No.	Description
231193	MRK-4426	44 RMU MRK cabinet frame, 26 in. deep with rear door
240798	MRK-4026	40 RMU MRK cabinet frame, 26 in. deep with rear door
240799	MRK-3726	37 RMU MRK cabinet frame, 26 in. deep with rear door
240796	MRK-2426	24 RMU MRK cabinet frame, 26 in. deep with rear door

### 31 1/2 IN. OUTSIDE DEPTH

Anixter No.	Vendor No.	Description
231198	MRK-4431	44 RMU MRK cabinet frame, 31 in. deep with rear door
240800	MRK-4031	40 RMU MRK cabinet frame, 31 in. deep with rear door
240801	MRK-3731	37 RMU MRK cabinet frame, 31 in. deep with rear door
240802	MRK-2431	24 RMU MRK cabinet frame, 31 in. deep with rear door

### 36 IN. OUTSIDE DEPTH

Anixter No.	Vendor No.	Description
240806	MRK-4436	44 RMU MRK cabinet frame, 36 in. deep with rear door
334389	MRK-4442	44 RMU MRK cabinet frame, 42 in. deep with rear door

### ACCESSORIES

Anixter No.	Vendor No.	Description
254081	MRK-Z4	Seismic bracket for MRK and VMRK cabinets

## WR Series Roll-out Rotating System

MIDDLE ATLANTIC PRODUCTS



Gain unrestricted access to equipment and cabling without the need for tracks and stands. Ideal for environments that require equipment bays to be placed up against walls or back to back, the award-winning WR allows entire bays of equipment to roll out and rotate for service and installation flexibility.

Continued on next page >>

## Rack, Console and Enclosure Solutions

# Middle Atlantic

(continued) WR Series Roll-out Rotating System

### FEATURES

- Slides out and rotates 60 degrees, requiring no additional accessories
- UL Listed in the U.S. and Canada
- Host enclosure can be preinstalled on-site while detachable rack frame is integrated with equipment off-site, simplifying installation
- 26 in. usable depth, 32 7/8 in. deep host enclosure
- 750 lb. weight capacity with proper weight distribution
- Effective cable-management system provided
- Knockouts provided for cable pass-through and ganging multiple racks
- Engineered ventilation locations optimize passive heat convection
- Configurable open top accepts a number of options for active thermal management
- Standard front and rear 11-gauge, 10-32 threaded rackrail with marked rack-space increments

### ROLL-OUT ROTATING RACK

Anixter No.	Vendor No.	Description
303393	WR-37-32	37 SP/32D
303394	WR-44-32	44 SP/32D

### SOLID FRONT DOOR FOR WR CABINET

Anixter No.	Vendor No.	Description
303395	WRFD-37	37 SP
303396	WRFD-44	44 SP

## CableSafe Data Wall Cabinet

MIDDLE ATLANTIC PRODUCTS



### FEATURES

- 26 in. width cabinet to allow space for patching
- Comes standard with wide-face rackrail on left and right of cabinet
- Optional off-set face rail for dressing to either side using included cable management rings or optional fiber spools
- Includes plexiglass door

Anixter No.	Vendor No.	Description
393132	CWR-12-17PD	12 RU tall, 17 in. deep
394305	CWR-18-17PD	18 RU tall, 17 in. deep
394307	CWR-26-17PD	26 RU tall, 17 in. deep
394310	CWR-12-22PD	12 RU tall, 22 in. deep
393134	CWR-18-22PD	18 RU tall, 22 in. deep
394313	CWR-26-22PD	26 RU tall, 22 in. deep
393133	CWR-12-26PD	12 RU tall, 26 in. deep
393135	CWR-18-26PD	18 RU tall, 26 in. deep
394315	CWR-26-26PD	26 RU tall, 26 in. deep

Anixter No.	Vendor No.	Description
394320	CWR-12-32PD	12 RU tall, 32 in. deep
394323	CWR-18-32PD	18 RU tall, 32 in. deep
393137	CWR-26-32PD	26 RU tall, 32 in. deep

## TOR Series Tilt-out Wall Rack

MIDDLE ATLANTIC PRODUCTS



Ideal for small sound systems, paging and patching applications in schools, hotels, offices or anywhere a secure, low-profile wall-mount solution is required.

Dimensions include usable depth 20 in., outside height 30 1/4 in., and outside width 24 1/2 in.

Anixter No.	Vendor No.	Description
303310	TOR-2-20SP	Racking height 3 1/2 in. (2-rack space), outside depth 4 7/16 in., surface-mount
303309	TOR-2-20RP	Racking height 3 1/2 in. (2-rack space), outside depth 4 7/16 in., recess-mount
303312	TOR-3-20SP	Racking height 4 1/4 in. (3-rack space), outside depth 6 3/16 in., surface-mount
303311	TOR-3-20RP	Racking height 4 1/4 in. (3-rack space), outside depth 6 3/16 in., recess-mount
303314	TOR-4-20SP	Racking height 7 in. (4-rack space), outside depth 4 15/16 in.
303313	TOR-4-20RP	Racking height 7 in. (4-rack space), outside depth 7 15/16 in.

## Horizontal Distribution Rack

MIDDLE ATLANTIC PRODUCTS



Upper bay mounts patch panels and pivots 100 degrees with positive stop for punch-downs. Lower bay mounts switches, hubs and routers and pivots 15 degrees for access to rear connections.

## FEATURES

- Integral electrical box for power distribution
- Vented, locking front door for mounting in nonsecure areas
- Multiple electrical knockouts to accommodate electrical conduit

Anixter No.	Vendor No.	Description
268472	HDR-4	3 1/2 in. x 3 1/2 in. (2-rack space x 2-rack space)
302499	HDR-FAN	External 4 1/2 in. fan kit

## Intermediate Distribution Rack

MIDDLE ATLANTIC PRODUCTS



Rack-mount hubs, routers and other equipment overhead in warehouses, retail outlets and other large, open-area locations.

## FEATURES

- Mounts overhead directly to unistrut beams or from trusses using threaded rods (not included)
- Dual exhaust fans extend equipment life
- Bottom plate can be machined in the field to mount wireless antennae, dome cameras and more
- Multiple UHF/VHF antenna knockouts on the bottom of the enclosure
- Grounding/bonding stud in top of enclosure facilitates proper grounding and bonding of electronic equipment, per NEBS and NEC standards
- Side knockouts for conduit pass-through to internal, standard electrical box
- Ships with included rack-mount power distribution unit, model #PD-915R
- Top includes four integral gland grommets for protecting cables and reducing dust within the enclosure
- Durable textured black powder-coat finish
- UL Listed in the U.S. and Canada

Anixter No.	Vendor No.	Description
354192	IDF-TM-1224BK	12 SP, truss mounted, 24 in. DP enclosure

## Clamping Rack Shelves

MIDDLE ATLANTIC PRODUCTS



Clamping rack shelves captivate components.

## FEATURES

- Available in 2- to 8-rack units
- 15 1/2 in. depth
- UL Listed in the U.S. and Canada

Anixter No.	Vendor No.	Description
231195	RC-2	2 RMU clamping rack shelf
231196	RC-3	3 RMU clamping rack shelf
231197	RC-4	4 RMU clamping rack shelf
240855	CAP5	8 3/4 in. (5 space), knock-down construction
240856	CAP6	10 1/2 in. (6 space), knock-down construction
240857	CAP7	12 1/4 in. (7 space), knock-down construction
240858	CAP8	14 in. (8 space), knock-down construction

## VSA Series Adjustable Telescoping Rack Shelf

MIDDLE ATLANTIC PRODUCTS



Unlike standard adjustable shelves, the entire VSA shelf telescopes to reach rear rail, providing a range of usable depths from 16 in. to 44 in. Providing the greatest usable depth in its class, the heavy-duty VSA is ideal for even the deepest components. Constructed of hemmed 16-gauge steel and finished in a durable black powder-coat finish, the VSA is fully vented for superior cooling and features many tie points for enhanced cable management. 500 lb. weight capacity.

Anixter No.	Vendor No.	Description
358800	VSA-1626	16 in. - 26 in. telescoping shelf
358801	VSA-2744	27 in. - 44 in. telescoping shelf

## Rack, Console and Enclosure Solutions

# Middle Atlantic

### Vented Universal Rack Shelves

MIDDLE ATLANTIC PRODUCTS



Featuring fully ventilated bottom and sides for heat dissipation, these fully welded, easy-to-install shelves fit all components up to 17 3/8 in. wide to quickly meet all of your rack-mounting needs. Made from 16-gauge steel, each unit is individually boxed. Includes three rear brackets to prevent components from sliding backward. This shelf helps to save valuable space by accepting the mounting of the PD-815SC-PBSH 8 outlet, 15 amp power strip on the rear of the shelf. Also allows the attachment of optional clamping bars to secure components.

Anixter No.	Vendor No.	Description
394300	U2V	3 1/2 in. (2-rack space), 17.44 in. W x 15 in. D., 50 lb.
394302	U3V	5 1/4 in. (3-rack space), 17.44 in. W x 15 in. D., 70 lb.
394303	U4V	7 in. (4-rack space), 17.44 in. W x 15.50 in. D., 85 lb.

### LCD Rack-mount

MIDDLE ATLANTIC PRODUCTS



#### FEATURES

- Generous front-to-back adjustment
- Versatile rack-mounting of LCD screen from 15 in. to 19 in., including some 20 in. monitors
- RM-LCD-MT can mount larger monitors, up to 32 in. depending on weight

Anixter No.	Vendor No.	Description
412963	RM-LCD-MV	9 SP, rack-mount, LCD, VESA
412964	RM-LCD-MT	9 SP, rack-mount, LCD, articulating
412965	RM-LCD-MK	9 SP, rack-mount, LCD, tilt mechanism

### Rack-mount Computer Keyboard

MIDDLE ATLANTIC PRODUCTS



#### FEATURES

- Includes high-quality keyboard
- Keyboard features built-in trackball and padded wrist-rests
- Hinged cable manager in rear
- Includes 12 ft. keyboard and trackball cable
- Occupies one space (1.75 in.)

Anixter No.	Vendor No.	Description
231232	RM-KB	Rack-mount computer keyboard, 1 RMU

### Heavy-duty D and TD Series Drawers

MIDDLE ATLANTIC PRODUCTS



Fully enclosed with inside dimensions measuring 15 7/8 in. wide by 14 1/2 in. deep, the D and TD series drawers feature spring-loaded latches and rugged, straightforward construction. Faceplates come with a textured black powder-coat or brushed and black anodized finish. Installed keylock option available.

#### BLACK BRUSHED AND ANODIZED FINISH

Anixter No.	Vendor No.	Description
231158	D2	2 RMU anodized finish rack-mount drawer
231161	D3	3 RMU anodized finish rack-mount drawer
231162	D4	4 RMU anodized finish rack-mount drawer
240885	D5	5 RMU anodized finish rack-mount drawer
229265	TD2	2 RMU textured finish rack-mount drawer
229293	TD3	3 RMU textured finish rack-mount drawer
229297	TD4	4 RMU textured finish rack-mount drawer
240974	TD5	5 RMU textured finish rack-mount drawer
303305	TD8FLK	8 RMU textured finish rack-mount file storage drawer with lock



**BLACK TEXTURED FINISH**

Anixter No.	Vendor No.	Description
229265	TD2	2 RMU textured finish rack-mount drawer
229293	TD3	3 RMU textured finish rack-mount drawer
229297	TD4	4 RMU textured finish rack-mount drawer
240974	TD5	5 RMU textured finish rack-mount drawer

**Rack-mount LCD Monitor With Keyboard and Touch Pad**

MIDDLE ATLANTIC PRODUCTS



Space-saving design occupies a single rack space. No-hassle one-year warranty. Easy-to-read bright active matrix LCD display. LCD can be in open position for system monitoring while keyboard is in the closed position. Standard 105-key keyboard with touch pad. 17 in. monitor is capable of supporting 1,280x1,024 screen resolution.

Anixter No.	Vendor No.	Description
319809	RM-KB-LCD17	Single space rack-mount 17 in. LCD monitor with keyboard and touch pad
369897	RM-KB-LCD17X8KV	Single space rack-mount 17 in. LCD monitor with keyboard, touch pad and 8-port KVM switch
369899	RM-KB-LCD17X16K	Single space rack-mount 17 in. LCD monitor with keyboard, touch pad and 16-port KVM switch
394380	PS2/USB-4C	PS/2 and USB cables, 4 pcs.

**LBX Series Lockboxes**

MIDDLE ATLANTIC PRODUCTS



Safely secure gear in Middle Atlantic's rack-mount LBX Series lockboxes. 9 in. deep, 3- and 4-space models are offered with a durable black powder-coat finish. UL Listed in the U.S. and Canada.

Anixter No.	Vendor No.	Description
231186	LBX-3	3 RMU lockbox, rack-mount
231188	LBX-4	4 RMU lockbox, rack-mount

**DLBX Series DVR Lockboxes**

MIDDLE ATLANTIC PRODUCTS



Optimized to handle the active or passive thermal-management needs of digital video recorders and other digital equipment. Configurable thermal-management system includes fan and two filters, and can be set up to accommodate the needs of any DVR. Optional proportional-speed thermostatic fan control ensures fan only runs when needed, reducing maintenance requirements and noise.

**FEATURES**

- Mounts vertically or horizontally to the wall, also can be used as a monitoring shelf
- Extensive cable management includes tie points, EKO's and cable pass-throughs
- Mechanically interlocking top provides added security yet removes easily for equipment servicing
- Standard key-locked solid hinging front door allows easy equipment access

Anixter No.	Vendor No.	Description
281779	DLBX	DVR lockbox with fan
281781	DLBX-WM	Pair of wall-mount brackets for DLBX
302259	DLBX-RR5	10-32 threaded rackrail kit for DLBX, 5-rack spaces with cutouts for cable pass-through
352618	FC-2-215-1C	Proportional-speed thermostatic fan control with two 15 amp outlets

**EB Series Blank Panels**

MIDDLE ATLANTIC PRODUCTS



**FEATURES**

- Flanged steel
- Durable powder-coat finish

Anixter No.	Vendor No.	Description
231178	EB1	1 RMU blank panel
231183	EB2	2 RMU blank panel
231187	EB3	3 RMU blank panel
231190	EB4	4 RMU blank panel
240849	EB5	5 RMU blank panel
240850	EB6	6 RMU blank panel

## Rack, Console and Enclosure Solutions

## Middle Atlantic

## VT Series Vent Panels

MIDDLE ATLANTIC PRODUCTS



## FEATURES

- Vent panels with high percentage of open area
- 16-gauge perforated steel
- Flanged for strength
- Durable black powder-coat finish

Anixter No.	Vendor No.	Description
240851	VT1	1 3/4 in. (1 space)
240852	VT2	3 1/2 in. (2 space)
240853	VT3	5 1/4 in. (3 space)
240854	VT4	7 in. (4 space)

## Perforated Security Covers

MIDDLE ATLANTIC PRODUCTS



Eliminate the prospect of any tampering with these tough security covers. Offered in large- or fine-perforation styles (models S and SF respectively), each cover is 1 in. deep.

## LARGE-PERFORATION STYLE

Allows unobstructed view of knob settings

Anixter No.	Vendor No.	Description
231271	S1	1 space (1 3/4 in.) panel
231275	S2	2 space (3 1/2 in.) panel
231277	S3	3 space (5 1/4 in.) panel
231278	S4	4 space (7 in.) panel

## FINE-PERFORATION STYLE

Allows sight of LEDs; most secure

Anixter No.	Vendor No.	Description
231290	SF1	1 RMU security panel
231292	SF2	2 RMU security panel
231293	SF3	3 RMU security panel
231294	SF4	4 RMU security panel

## Brush Grommet Panels

MIDDLE ATLANTIC PRODUCTS



The brush grommet panels provide a clean, organized cable-entry method when used in conjunction with any work surface. Features a built-in cable-management tray. Available in one- and two-space versions. Two-space brush grommet panel fits in opening on all MW Series top options.

Anixter No.	Vendor No.	Description
302118	BR1	1 RMU brush panel for cable pass-through
334554	BR2	2 RMU brush panel for cable pass-through

## Cable Management Bars

MIDDLE ATLANTIC PRODUCTS



The economical and effective way to manage cable horizontally. Made from 1/4 in. diameter flattened rod (model LBP-1R, LBP-1.5 and model LBP-1R4) or 3/16 in. thick aluminum (model LBP-1S), each bar provides convenient cable tie points.

Anixter No.	Vendor No.	Description
231182	LBP-1R	Round horizontal lacing bars, 10-pack
231185	LBP-1S	Square horizontal lacing bars, 10-pack
240884	LBP-1.5	1.5 in. offset round rod, 10-pack
231184	LBP-1R4	4 in. offset round rod, 10-pack
231181	LBP-1A	L bar, 10-pack
290517	LBP-2A	2 in. offset L style lacing bars, 10-pack
290518	LBP-4A	4 in. offset L style lacing bars, 10-pack
290519	LBP-6A	L bar, 6 in. offset, 10-pack
305193	LBP-LTF	2 RMU lacing panel, 10-pack

# Middle Atlantic

## Horizontal Cable Management

MIDDLE ATLANTIC PRODUCTS



### FEATURES

- Available in a variety of styles to suit any application
- Welded-steel construction
- Finished in durable black powder-coat finish

Anixter No.	Vendor No.	Description
231106	HCM-1	1 RMU
231109	HCM-1D	1 RMU, large D-Rings
231111	HCM-1DR	1 RMU, front and rear D-Rings
231117	HCM-1V	1 3/4 in. (1 space) micro-clip style, end rings
231115	HCM-1DV	1 3/4 in. (1 space) D-Ring style, end rings
231119	HCM-2D	2 RMU, large D-Rings
231121	HCM-2DR	2 RMU, front and rear D-Rings
231123	HCM-2DV	3 1/2 in. (2 space) D-Ring style, end rings
231163	D-RING	Wall-mount/rack-mount D-Ring style

## Plastic Horizontal Cable Managers

MIDDLE ATLANTIC PRODUCTS



### FEATURES

- Matches and integrates well with PCD Series Ducts
- Comes with removable hinged cover
- Available in single piece and four packs

Anixter No.	Vendor No.	Description
421707	PHCM-1-2	One space and 2 in. depth
421708	PHCM-1-4	One space and 2 in. depth
421709	PHCM-2-3	Two space and 3 in. depth
421710	PHCM-1-2-P4	Four pack with one space and 2 in. depth
421711	PHCM-1-4-P4	Four pack with one space and 4 in. depth
421712	PHCM-2-3-P4	Four pack with two space and 3 in. depth

## PCD Series Plastic Cable Managers

MIDDLE ATLANTIC PRODUCTS



Flexible application for vertical cable management on open frame racks. Plastic cable ducts provide a cost-effective solution to protect, route and organize data cables, patch cords and power cords.

### FEATURES

- Available in 1 1/2 in., 2 in., 3 in. and 4 in. widths
- Available in 2 in., 3 in. and 4 in. depths; single channel and 6 in. and 8 in. depths; dual channel
- 38-, 45- and 51-split space heights available for all two-post and four-post racks
- Slotted-finger design allows for horizontal cable access exactly where it's needed
- Fingers can be easily removed for larger capacity
- Plastic covers provide organization while keeping cables hidden

Anixter No.	Vendor No.	Description
421713	PCD-1.5X2-4BK	1.5 in. W x 2 in. D x 41RU, single, four pieces
421719	PCD-1.5X4-4BK	1.5 in. W x 4 in. D x 41RU, single, four pieces
421720	PCD-2-3-51SC	2 in. W x 3 in. D x 51RU, single
421722	PCD-2-3-45SC	2 in. W x 3 in. D x 45RU, single
421723	PCD-2-3-38SC	2 in. W x 3 in. D x 38RU, single
421724	PCD-2-3-30SC	2 in. W x 3 in. D x 30RU, single
421726	PCD-2-3-25SC	2 in. W x 3 in. D x 25RU, single
421728	PCD-2-3-20SC	2 in. W x 3 in. D x 20RU, single
421731	PCD-2-3-15SC	2 in. W x 3 in. D x 15RU, single
421733	PCD-2-3-12SC	2 in. W x 3 in. D x 12RU, single
421734	PCD-2-3-8SC	2 in. W x 3 in. D x 8RU, single
421735	PCD-3-3-51SC	3 in. W x 3 in. D x 51RU, single
421736	PCD-3-6-51DC	3 in. W x 6 in. D x 51RU, dual
421737	PCD-3-3-45SC	3 in. W x 3 in. D x 45RU, single
421738	PCD-3-6-45DC	3 in. W x 6 in. D x 51RU, dual
421739	PCD-3-3-38SC	3 in. W x 3 in. D x 38RU, single
421740	PCD-3-6-38DC	3 in. W x 6 in. D x 38RU, dual
421741	PCD-4-4-51SC	4 in. W x 4 in. D x 51RU, single
421742	PCD-4-8-51DC	4 in. W x 8 in. D x 51RU, dual
421743	PCD-4-4-45SC	4 in. W x 4 in. D x 45RU, single
421744	PCD-4-8-45DC	4 in. W x 8 in. D x 45RU, dual
421745	PCD-4-4-38SC	4 in. W x 4 in. D x 38RU, single
421746	PCD-4-8-38DC	4 in. W x 8 in. D x 38RU, dual

# Middle Atlantic

## Hinged Horizontal Cable Managers

MIDDLE ATLANTIC PRODUCTS



### FEATURES

- Dress cables between open frame racks and other enclosures
- Cable-strain relief provides more reliable connections
- Multiple cable pass-throughs: top, rear, bottom and sides
- Solid face conceals cables from view
- Hinged panel allows easy entry for and access to cable bundles

Anixter No.	Vendor No.	Description
336582	HHCM-1	1-rack space
268463	HHCM-2	2-rack space

## QFP Series Quiet Fan Panel Assemblies

MIDDLE ATLANTIC PRODUCTS



### FEATURES

- Three RMU space, includes fans and grills
- UQFP Series are two space panels with either two or four fans
- Available with or without the LED temperature display, fan-failure notification and remote over-temp notification

#### ANODIZED

5 1/4 in. high (three RMU space)

Anixter No.	Vendor No.	Description
231194	QFP-2	Two fan, free air dB rating < 33 dB
231171	QFP-1	One fan, free air dB rating < 30 dB

#### TEXTURED

Anixter No.	Vendor No.	Description
243125	OTFP-2	Two fan, 5 1/4 in. high (three space), free air dB rating < 33 dB
243126	OTFP-1	One fan, 5 1/4 in. high (three space), free air dB rating < 30 dB
326261	UQFP-2D	50 cfm fan panel with LED display, remote failure notification, overtemp alarm
326262	UQFP-4D	100 cfm fan panel with LED display, remote failure notification, overtemp alarm
326260	UQFP-2	50 cfm fan panel, overtemp alarm
325467	UQFP-4	100 cfm fan panel, overtemp alarm

## W5701 Sight-Line Console

WINSTED



Sight-Line consoles allow flexibility and expandability in console configurations to fit any space requirement, user need or budget. In today's demanding control rooms, monitor viewing angles and operator sight lines are critical to long-term success. To address this issue, Sight-Line consoles feature Winsted's new integrated Versa-Trak monitor-array system, which offers the ultimate in adjustability. The Versa-Trak system permits users to optimize, and easily modify, sight lines and viewing angles based on personal needs. Sight-Line is a beautiful console with a feature-set second to none. The W5701 is just a sample of Sight-Line's flexibility. Let us design the perfect solution for you.

## FEATURES

- Versa-Trak monitor-mounting system
- Integrated data/power provisions
- Easy-access cable management
- Doors with CPU shelf for convenient swing-out access

Contact your local sales representative for ordering information.

## Insight Console

WINSTED



Winsted's compact console features a high-density profile designed for a high-performance world. Insight's overall depth of 32 in. saves valuable space and maximizes control room functionality. Our engineers reduced the depth of both the chase and the work surface on the popular Sight-Line console to create a solution with a more efficient footprint that meets ergonomic standards, and provides ample desktop workspace. This configuration is just a sample of Insight's flexibility. Whether you need a single workstation, or a complete control room, Insight is the perfect solution. Let us design a console just for you.

## FEATURES

- Versa-Trak monitor-mounting system
- Integrated data/power provisions
- Easy-access cable management
- Doors with CPU shelf for convenient swing-out access

Contact your local sales representative for ordering information.

## Ascend Sit/Stand Console

WINSTED



Winsted's sit/stand console offers three programmable height settings for ultimate versatility and optimum comfort in any control room setting. This completely redesigned sit/stand console includes electric-lift legs, which enable operators to quickly and easily adjust the work-surface height from 29 in. to 44 in. with the push of a button. Two-, three- and four-leg systems are available with load capacities of 300 lb., 450 lb. and 600 lb. respectively. This is just one example of an Ascend sit/stand solution. Let us design a console specifically for you, and take your control room to new heights with Ascend.

## FEATURES

- Electric-lift legs with three programmable height settings
- Versa-Trak monitor-mounting system
- Easy-access cable management
- Doors with CPU shelf for convenient swing-out access

Contact your local sales representative for ordering information.

## E4858 Encompass II Workstation

WINSTED



This unique workstation fits every environment from multimedia, to video, to security and office settings. Bring your work envelope closer to you. Encompass your surroundings with this workstation for maximum work performance. Choose from popular in-stock components, or create a customized look. Designed for efficient workspace comfort. The E4858 is just one example of Winsted's Encompass II product line. Choose from many other preconfigured models, or let us design the perfect solution for you.

## FEATURES

- Upscale look with exceptional value
- Modular and easy to reconfigure
- Wide variety of accessories
- In stock and ready to ship

Contact your local sales representative for ordering information.

## Rack, Console and Enclosure Solutions

## Winsted

## E4860 Surveillance Workstation

WINSTED



The E4860 provides a compact, economical solution for supporting your electronics. This ergonomic workstation enhances the workspace environment while maximizing both operator performance and operator comfort. Customized workstations offer a personal touch, with expanding possibilities in the future. The E4860 is just one option. Winsted has many other workstations to choose from.

**FEATURES**

- Dual 14U rack-mount cabinets
- Two quad-monitor mounts
- Durable work surface with contour edge molding
- In stock and ready to ship

Contact your local sales representative for ordering information.

## M-View Monitor Wall

WINSTED



Winsted's M-View is a custom-built, extruded-aluminum monitor wall that is flexible and completely modular. Each M-View is designed and manufactured to support your specific monitor configuration and fit in your unique space. The M-View is fabricated from lightweight, high-strength extruded aluminum with a black anodized finish. The monitor wall can support any size LCD and/or plasma screen and can be configured as an in-line, concave or convex mounting solution. The M-View seamlessly integrates technology and space to optimize viewing angles, improve operator comfort and increase productivity. This configuration is just an example of M-View's flexibility.

**FEATURES**

- In-stock and custom monitor walls available
- Easy to reconfigure and expand with changing technology
- Constructed of black anodized extruded aluminum
- Integrated power strips and cable management

Contact your local sales representative for ordering information.

## G5305 LCD/3 Console

WINSTED



LCD/3 Consoles target the low-profile demands of today's command centers, reception areas, surveillance areas and control rooms. Put your LCD application into single-, double- or triple-tier modular consoles. LCD/3 Consoles are ergonomically designed for the flat-panel market and expand easily with your growing needs. The G5305 is just one example of Winsted's LCD/3 product line. Choose from several other preconfigured models.

**FEATURES**

- Low-profile for unobstructed view over console
- Ergonomically correct viewing angle
- EIA 19 in. rack-mount openings
- Many user-friendly accessories to choose from

Contact your local sales representative for ordering information.

## W5831 Slat-Wall Console

WINSTED



Winsted's Slat-Wall console is built on the same foundation as the award-winning Sight-Line console. The same world-class feature set is incorporated with slat-wall to provide added versatility and an element of privacy. The Slat-Wall is 15 in. tall and constructed of high-quality extruded 6105-T5 aluminum. The black anodized finish is attractive and smooth to the touch. A variety of monitor mounts and user-friendly accessories are available to mount on the Slat-Wall. Slat-Wall consoles are modular, reconfigurable and expandable. Let us design the perfect solution for your security control room.

**FEATURES**

- Slat-wall mounting system
- Integrated data/power provisions
- Easy-access cable management
- Doors with CPU shelf for convenient swing-out access

Contact your local sales representative for ordering information.