

# LANscape® Solutions

## LANC/LANS Panels

### FASTSHIP

Do you require fibre optic patch panel solutions that save you time and money during installation and are quickly available? Would you like to receive your panel equipped with adapter modules or even fully equipped including pigtailed? With our assorted FAST LANC/LANS panels (please see below table), we are providing expedited shipping on your day-to-day product needs, within 72 hours ready to ship, from our fast assembly lines and in-stock product assortment.

#### 1U LANC Fixed Fibre Housing

- **Quick-mount feature (teardrop design)**  
*Allows quick and accurate mounting of housing*
- **Accommodates different termination methods**  
*Pigtail splicing or field termination with UniCam® in the same housing*

#### 1U LANS Sliding, Tilting Fibre Housing

- **Quick-mount feature (teardrop design)**  
*Allows quick and accurate mounting of housing*
- **Flexible interior of housing**  
*Suitable for pigtail splicing, pre-terminated cables and Plug & Play™ or Pretium EDGE® trunks, field termination with UniCam® connectors, or use of FutureCom™ S250/S500 copper jacks*
- **Modular back (two openings) to strain-relief different cable types**  
*Use of PG glands for outer cable diameter 6-16 mm (maximum four), mounting clips for furcation heads of pre-terminated cables (maximum four), low-fibre-count cables (maximum 24)*



#### Terms and Conditions

- The FastShip programme is designed to support day-to-day small works including moves, adds, and changes (MACs). FastShip products will be available to ship within 72 hours from the date of Corning's purchase order confirmation. Expedited freight terms are available on request at the customer's own cost and expense.
- All FastShip programme products are available on a first-come, first-serve basis. If there is no availability at any given time, Corning reserves the right to offer deviant lead times for the earliest possible date or suggest equivalent alternatives.

# LANC/LANS Panels – Available Configurations

## LANC Fixed Fibre Housing - partially loaded

Breakout Version: Equipped with fibre adapter modules (LC Duplex with integrated shutters), PG gland (1x M20), blanks for unused front openings, no splice protectors

Adapter & Fibre Type	Part Number	Description
LC Duplex SM/OS2	LANC-112-AE-00R-S0B	LANC, 1U, 12 Fibres, LC duplex blue, SM/OS2, without splice trays and pigtails, black
	LANC-124-AE-00R-S0B	LANC, 1U, 24 Fibres, LC duplex blue, SM/OS2, without splice trays and pigtails, black
	LANC-148-AE-00R-S0B	LANC, 1U, 48 Fibres, LC duplex blue, SM/OS2, without splice trays and pigtails, black
LC Duplex MM/OM4	LANC-112-AD-00Q-S0B	LANC, 1U, 12 Fibres, LC duplex aqua, MM/OM4, without splice trays and pigtails, black
	LANC-124-AD-00Q-S0B	LANC, 1U, 24 Fibres, LC duplex aqua, MM/OM4, without splice trays and pigtails, black
	LANC-148-AD-00Q-S0B	LANC, 1U, 48 Fibres, LC duplex aqua, MM/OM4, without splice trays and pigtails, black
SC Duplex SM/OS2	LANC-112-72-00R-S0B	LANC, 1U, 12 Fibres, SC duplex blue, SM/OS2, without splice trays and pigtails, black
	LANC-124-72-00R-S0B	LANC, 1U, 24 Fibres, SC duplex blue, SM/OS2, without splice trays and pigtails, black
SC Duplex MM/OM4	LANC-112-E7-00Q-S0B	LANC, 1U, 12 Fibres, SC duplex aqua, MM/OM4, without splice trays and pigtails, black
	LANC-124-E7-00Q-S0B	LANC, 1U, 24 Fibres, SC duplex aqua, MM/OM4, without splice trays and pigtails, black



## LANS Sliding Fibre Housing - partially loaded

Breakout Version: Equipped with fibre adapter modules (LC Duplex with integrated shutters), PG gland (1xM20), blank covers for unused front openings, no splice protectors

Adapter & Fibre Type	Part Number	Description
LC Duplex SM/OS2	LANS-112-AE-00R-S0B	LANS, 1U, 12 Fibres, LC duplex blue, SM/OS2, without splice trays and pigtails, black
	LANS-124-AE-00R-S0B	LANS, 1U, 24 Fibres, LC duplex blue, SM/OS2, without splice trays and pigtails, black
	LANS-148-AE-00R-S0B	LANS, 1U, 48 Fibres, LC duplex blue, SM/OS2, without splice trays and pigtails, black
LC Duplex OM4	LANS-112-AD-00Q-S0B	LANS, 1U, 12 Fibres, LC duplex aqua, MM/OM4, without splice trays and pigtails, black
	LANS-124-AD-00Q-S0B	LANS, 1U, 24 Fibres, LC duplex aqua, MM/OM4, without splice trays and pigtails, black
	LANS-148-AD-00Q-S0B	LANS, 1U, 48 Fibres, LC duplex aqua, MM/OM4, without splice trays and pigtails, black
SC Duplex SM/OS2	LANS-112-72-00R-S0B	LANS, 1U, 12 Fibres, SC duplex blue, SM/OS2, without splice trays and pigtails, black
	LANS-124-72-00R-S0B	LANS, 1U, 24 Fibres, SC duplex blue, SM/OS2, without splice trays and pigtails, black
SC Duplex MM/OM4	LANS-112-E7-00Q-S0B	LANS, 1U, 12 Fibres, SC duplex aqua, MM/OM4, without splice trays and pigtails, black
	LANS-124-E7-00Q-S0B	LANS, 1U, 24 Fibres, SC duplex aqua, MM/OM4, without splice trays and pigtails, black



## LANS Sliding Fibre Housings - fully equipped, ready to splice

Splice Version: Equipped with fibre adapter modules (LC Duplex with integrated shutters), splice trays including splice organisers, pigtails and cover, PG gland (1x M20), blank covers for unused front openings, no splice protectors

Adapter & Fibre Type	Part Number	Description
LC Duplex SM/OS2	LANS-112-AE-02R-S8B	LANS, 1U, 12 Fibres, LC duplex blue, SM/OS2, including splice trays and pigtails, black
	LANS-124-AE-02R-S8B	LANS, 1U, 24 Fibres, LC duplex blue, SM/OS2, including splice trays and pigtails, black
	LANS-148-AE-02R-S8B	LANS, 1U, 48 Fibres, LC duplex blue, SM/OS2, including splice trays and pigtails, black
LC Duplex MM/OM4	LANS-112-AD-03Q-S8B	LANS, 1U, 12 Fibres, LC duplex aqua, MM/OM4, including splice trays and pigtails, black
	LANS-124-AD-03Q-S8B	LANS, 1U, 24 Fibres, LC duplex aqua, MM/OM4, including splice trays and pigtails, black
	LANS-148-AD-03Q-S8B	LANS, 1U, 48 Fibres, LC duplex aqua, MM/OM4, including splice trays and pigtails, black
SC Duplex SM/OS2	LANS-112-72-58R-S8B	LANS, 1U, 12 Fibres, SC duplex blue, SM/OS2, including splice trays and pigtails, black
	LANS-124-72-58R-S8B	LANS, 1U, 24 Fibres, SC duplex blue, SM/OS2, including splice trays and pigtails, black
SC Duplex MM/OM4	LANS-112-E7-39Q-S8B	LANS, 1U, 12 Fibres, SC duplex aqua, MM/OM4, including splice trays and pigtails, black
	LANS-124-E7-39Q-S8B	LANS, 1U, 24 Fibres, SC duplex aqua, MM/OM4, including splice trays and pigtails, black



## Splice Packs

For use with LANC or LANS partially loaded breakout versions, including splice organisers, pigtails, and cover, no splice protectors

Adapter & Fibre Type	Part Number	Description
LC SM/OS2	SP12-02R-S8	LC SM/OS2 UPC Universal Splice Pack (heat-shrink/crimp) including 12 pigtails and cover
LC MM/OM4	SP12-03Q-S8	LC MM/OM4 Universal Splice Pack (heat-shrink/crimp) including 12 pigtails and cover
SC SM/OS2	SP12-58R-S8	SC SM/OS2 UPC Universal Splice Pack (heat-shrink/crimp) including 12 pigtails and cover
SC MM/OM4	SP12-39Q-S8	SC MM/OM4 Universal Splice Pack (heat-shrink/crimp) including 12 pigtails and cover



## Splice Protection

Adapter & Fibre Type	Part Number	Description
	HSP-60S100-1	Heat-shrink Protectors, 60 mm (pack of 100)
	CSP-1	Crimp Splice Protectors (150 pcs)