



EVID

C O M P A C T S O U N D

SUPERB SOUND MADE SIMPLE

 Electro-Voice

A blurred photograph of a restaurant interior. In the foreground, a dark wooden table is set with a folded white napkin on a small plate, a tall clear glass, and a white candle in a glass holder. The background is out of focus, showing several people sitting at tables and a person standing near a window. The lighting is warm and ambient.

**SUPERB  
SOUND  
MADE  
SIMPLE**

FLEXIBLE, SCALABLE BACKGROUND MUSIC (BGM) SOLUTION FOR A WIDE RANGE OF ARCHITECTURAL ENVIRONMENTS, INCLUDING RETAIL SPACES, OFFICES, AND RESTAURANTS.



**FIVE INTERCHANGEABLE MODELS OFFER FLEXIBLE COMBINATIONS FOR BIGGER SOUND, SMALLER SIZE, AND EASY INSTALLATION**

The new EVID Compact Sound speaker series joins the globally popular EVID (EV Innovative Design) family of small-format installed audio products from Electro-Voice.

EVID Compact Sound is designed to offer an unparalleled performance-to-size ratio in the small-format installed sound category. The series includes five sonically and aesthetically matched models which allow complete systems to be customized more effectively and more economically: subwoofer and satellite speakers for surface-mounting, subwoofer and satellite speakers for ceilings, and a pendant speaker.

Individual models may be mixed with one another for optimal results according to application, and all stand apart from other available products by providing a unique combination of superior EV sound quality, stylish design, smaller size, and simpler installation.



**BALANCED CROSSOVER CIRCUITS**

SEAMLESSLY BLEND THE OUTPUT OF THESE HIGH-QUALITY LOUDSPEAKERS SO THAT THE AUDIO SYSTEM SEEMS TO DISAPPEAR, LEAVING ONLY THE MUSIC.



# SUPERB SOUND MADE SIMPLE

For more information, visit [www.electrovoice.com](http://www.electrovoice.com)



## COMMON SYSTEM FEATURES

- “BGM” in a box: Purchase either a complete pre-packaged system or mix-and-match satellite models with any subwoofer to meet décor or installation requirements.
- Direct connection of satellites to subwoofer — substantially simplifies wiring.
- Subs feature a large 8” woofer for increased LF output and more pleasing sound at lower volumes.
- Supports 100 W, 70/100 V, and 4/8 ohm audio connections.



## SURFACE-MOUNT FEATURES

- Simplified mounting design for satellites — enables quicker installation while allowing for significant articulation and range of motion.
- Attractive subwoofer design with full-face grille — blends in to environment.
- Supports stereo operation with 8-ohm audio connections.
- Quick-mount slide-on wall bracket included.
- Compact sub and satellites offer surprising performance-to-size ratio.
- Available in black or white finishes.



Ceiling sub input panel



Ceiling sub grille off



Surface sub wall-bracket mount




## CEILING FEATURES

- Quick-install design with captive mounting tabs to fit nearly any ceiling construction.
- Four-pin Phoenix connectors on ceiling satellite speakers support pass-thru wiring.
- UL 2043/1480 ratings allow for use in signaling applications and plenum air spaces.
- Ceiling cutout templates and all mounting accessories included.
- Available in white finish.

## PENDANT-MOUNT FEATURES

- 2" full-range transducer — acoustically matched to ceiling and surface-mount satellite versions.
- Attractive compact design.
- Concealed wire connection with pass-thru Phoenix plug for easy wiring.
- UL-rated quick-mount pendant cable included.
- Designed to be exclusively used with either the Compact Sound Ceiling or Surface mount subwoofers.
- Available in white finish.

\* Products not shown to scale.



Surface sub input panel



Surface satellite wall-bracket arm



Surface satellite input panel

## SUPERB SOUND MADE SIMPLE

SPECIFICATIONS	EVID 40S (surface-mount sub)	EVID 2.1 (surface-mount satellite)	EVID 40C (ceiling sub)	EVID C2.1 (ceiling satellite)	EVID P2.1 (pendant mount)
<b>Frequency Response (-10 dB)</b>	42 Hz – 300 Hz	180 Hz – 20 kHz	45 Hz – 300 kHz	180 Hz – 20 kHz	180 Hz – 20 kHz
<b>Power Handling</b>	200 W	30 W	200 W	30 W	30 W
<b>Sensitivity</b>	88 dB	84 dB	88 dB	84 dB	84 dB
<b>Impedance</b>	Dual 8 ohm / mono 4 ohm	16 ohms	mono 4 ohms	16 ohms	16 ohms
<b>Maximum SPL</b>	114 dB	100 dB	114 dB	100 dB	100 dB
<b>Voice Coverage (H x V)</b>	Omnidirectional	150° x 150°	Omnidirectional	150° x 150°	150° x 150°
<b>Music Program Coverage (H x V)</b>	Omnidirectional	100° x 100°	Omnidirectional	100° x 100°	100° x 100°
<b>Transducer</b>	200 mm (7.87 in)	50 mm (1.97 in)	200 mm (7.87 in)	50 mm (1.07 in)	50 mm (1.07 in)
<b>Bracket Adjustment Range (H x V)</b>	Fixed	160° x 60°	N/A	N/A	N/A
<b>Connectors</b>	Phoenix (2-pin)	Phoenix (2-pin)	Phoenix (2-pin)	Phoenix (4-pin)	Phoenix (4-pin)
<b>Enclosure</b>	Wood (MDF)	ABS (fire rated)	Steel & ABS (fire rated)	Steel & ABS (fire rated)	ABS (fire rated)
<b>Transformer Taps</b>	100 W, 50 W, 25 W, 12.5 W	N/A	100 W, 50 W, 25 W, 12.5 W	N/A	N/A
<b>Dimensions (H x W x D)</b>	400 mm x 400 mm x 230 mm (15.75 in x 15.75 in x 9.06 in)	115 mm x 85 mm x 95 mm (4.53 in x 3.35 in x 3.75 in)	316 mm x 373 mm (12.44 in x 14.69 in)	119 mm x 135 mm (4.7 in x 5.3 in)	201 mm x 113 mm (7.92 in x 4.45 in)
<b>Net Weight (Individual Units)</b>	12.05 kg (26.55 lb)	0.5 kg (1.1 lb)	9.52 kg (21 lb)	0.82 kg (1.8 lb)	0.73 kg (1.6 lb)
<b>Shipping Weight</b>	1 sub and 4 satellites: 18.26 kg (40.25 lb)		1 sub and 4 satellites: 19.05 kg (42 lb)		2.04 kg (4.5 lb) per pair
<b>Included Accessories</b>	Wall bracket; hex wrench	Wall bracket; hex wrench	C-Ring, Tile Rails	C-Ring	Suspension cable

# EVID COMPACT SOUND



Headquarters Americas:  
 Bosch Security Systems, Inc.  
 12000 Portland Ave South | Burnsville, MN 55337 | USA  
 Ph: 1 800 289 0096 | Fax: 1 800 955 6831  
[buv.orders@us.bosch.com](mailto:buv.orders@us.bosch.com)