

### **Network Video Recorder Naming Rule**






### **Network Video Recorder Naming Rule**




### **Digital Video Recorder Naming Rule**







### **Digital Video Recorder Naming Rule**



# **Digital Camera Naming Rule**



### **Digital Camera Naming Rule**




### **Digital Camera Naming Rule**

# DS-2CD2742FWD - IZSB


Auto Back Focus - Usually found on the box cameras Black camera housing IR - Camera has built in Infrared 13 IR3 - Camera has built in Infrared up to 30meters 15 IR5 - Camera has built in Infrared up to 50 meters P-iris lens Motorized Vari-Focal lens Heater Serial I/O (Audio, alarm I/O) 8-32mm Motorized zoom lens (standard 2.8 – 12mm) Vandal Resistant Body / Outdoor Version W Wi-fi - Built in wireless antenna Body has 2 connections (Covert camera body – supports 2 lenses) -L10 Cylindrical lens / sensor (Covert Camera) -L20 L-Shaped lens / sensor (Covert Camera) -L30 Tube shaped lens / sensor (Covert Camera) -L40 Eye-Ball shaped lens / sensor (Covert Camera)

HIKVISION


# **PTZ Naming Rule**




### **PTZ Naming Rule**



# **Analog Camera Naming Rule**



### **Analog Camera Naming Rule**



# **Analog Camera Naming Rule**

# DS-2CE16D7T - AIR3ZH

Dual Voltage - Supports both 24 VAC and 12 VDC Black camera housing Camera has built in Infrared **IR** Camera has built in Infrared IR3 Camera has built in Infrared up to 30meters IT Camera uses FXIR IT3 Camera uses EXIR up to 40 meters IT5 Camera uses EXIR up to 80 meters VF Manual Vari-Focal lens **VP** Vandal Resistant - Outdoor Rated Motorized Vari-Focal lens Heater Metal Body camera