

High Density

Outlet configuration allows full length SKU's fit within 42U rack with top, bottom, or front exit cable

Low Profile Design

Industry leading design saves rack space and ensures good access

Hot Swappable Network Module

With Large OLED And Graphics for easy Phases Load Balancing



Redundant Network Access (RNA)

In 2N configuration for network redundancy or tenant/client use

Power and Energy Metering

(V,A,VA, W,KWh,pf) to +/- 1% billing-grade accuracy

Color Coded Outlets and Circuit Breakers

For easy source Identification

USB Port

FW Upgrade / Configuration



Premium Hydraulic-Magnetic Circuit Breakers

Stable trip characteristics at extreme temperatures

Designed for High Temperature

Safe, Reliable Operation at 60°C with Full Load Rating

Best-in-Class Billing Grade Accuracy

+/- 1% throughout entire range of operational spec



Daisy Chain

Up to 4 PDUs and 32 sensors



Environmental & Security

Ready with support for up to 8 digital plug-and-play sensors or proximity card access

Locking IEC Outlets

Provide secure power connection with optional locking cords or integrated locking features