

VL562SD 3.6mm lens

Features

- View sideways at 45° angle or straight down
- 5 year warranty

Specifications

Image Sensor	1/4" color CCD
Resolution.....	420 lines
Minimum Illumination.....	0.01 lux
Electronic Shutter	Auto: 1/60 sec. – 1/100,000 sec.
Video Output Level	1.0Vp.p, 75 Ohm
S/N Ratio	Greater than 50dB
Output.....	Video - BNC, Power -DC jack
Operating Temperature/ Humidity.....	14° F – 122° F / within 90% RH
Power Consumption	110mA
Power Supply	12VDC regulated (UL and CSA power supply listed included)
Dimensions.....	3.4" (Dia.) x 1.6" (H)
Weight	2 oz.

