

# SMARTONLINE® UNITY PF UPS — MORE POWER IN LESS SPACE



You buy a UPS to avoid problems, so it's maddening when it actually causes headaches, backaches and even downtime. Finally, there's an intelligent, networked UPS that lightens your workload while protecting critical equipment from unexpected power loss:

- Smart batteries provide accurate runtime data throughout their lifespan
- Batteries also record first-use date for proactive battery replacement alerts that prevent battery failure downtime
- Self-aligning blind-mate connections for batteries and bypass PDUs enable lighter, easier single-person installation and maintenance without downtime or need for electrician assistance
- Controllable outlet banks with programmable auto-probe feature provides remote automated load control for self-healing device reboots and runtime prioritization during outages

## 5kVA On-Line UPS Specifications: Tripp Lite vs. Competitors

Model	VA	Watts	Rack Size	Input Voltage	Output Voltage	Full-Load Runtime (min.)	Half-Load Runtime (min.)	Maint. Bypass	Included Input Options	Outlet Types	Outlet Control
Tripp Lite – All models feature unity (1.0) power factor, pure sine wave output, ENERGY STAR® 2.0, SNMP card, easy-access management console, temperature-compensated charging and front-panel LCD.											
<a href="#">SU5KRT3UHV</a>	5000	5000	3U	208/240	208/240	4.9 (5000W)	14.1 (2500W)	No	Hardwire or L6-30P	NEMA + Hardwire	2 Banks
<a href="#">SU5KRT3UHVMB</a>	5000	5000	3U	208/240	208/240	4.9 (5000W)	14.1 (2500W)	Yes	Hardwire or L6-30P	NEMA + Hardwire	2 Banks
<a href="#">SU5KRT3UTE</a>	5000	5000	5U	208	208 + 120	4.9 (5000W)	14.1 (2500W)	No	Hardwire or L6-30P	NEMA + Hardwire	2 Banks
<a href="#">SU5KRT3UTFMB</a>	5000	5000	5U	208	208 + 120	4.9 (5000W)	14.1 (2500W)	Yes	Hardwire or L6-30P	NEMA + Hardwire	2 Banks
<a href="#">SU5KRT3UG</a>	5000	5000	3U	200-240	200-240	4.9 (5000W)	14.1 (2500W)	No	Hardwire Only	IEC + Hardwire	2 Banks
<a href="#">SU5KRT3UGMB</a>	5000	5000	3U	200-240	200-240	4.9 (5000W)	14.1 (2500W)	Yes	Hardwire Only	NEMA + Hardwire	2 Banks
<a href="#">SU5KRT3UHW</a>	5000	5000	3U	200-240	200-240	4.9 (5000W)	14.1 (2500W)	No	Hardwire Only	Hardwire Only	No
<a href="#">SU5KRT3UHWMB</a>	5000	5000	3U	200-240	200-240	4.9 (5000W)	14.1 (2500W)	Yes	Hardwire Only	Hardwire Only	No
<a href="#">SU5KRT3UX</a>	5000	5000	3U	220/230/240	220/230/240	4.9 (5000W)	14.1 (2500W)	No	Hardwire Only	IEC + Hardwire	2 Banks
APC®											
SRT5KRMXLTL	5000	4800	3U	208/240	208/240	3.5 (4800W)	10.7 (2400W)	No	L6-30P	NEMA	No
SRT5KRMXLTL-5KTF	5000	4800	5U	208/240	208/240 + 120	3.5 (4800W)	10.7 (2400W)	No	L6-30P	NEMA	No
SRT5KRMXLTLUS	5000	4800	3U	208/240	208/240	3.5 (4800W)	10.7 (2400W)	No	L6-30P	NEMA	No
SRT5KRMXLTL-IEC	5000	4800	3U	208/240	208/240	3.5 (4800W)	10.7 (2400W)	No	L6-30P	IEC	No
SRT5KXLT	5000	4800	Tower	208/240	208/240	3.5 (4800W)	10.7 (2400W)	No	L6-30P	NEMA	No
SRT5KXLT-5KTF	5000	4500	Tower	208/240	208/240 + 120	4.0 (4500W)	11.8 (2250W)	No	Hardwire Only	NEMA	No
SRT5KXLTUS	5000	4800	Tower	208/240	208/240	3.5 (4800W)	10.7 (2400W)	No	L6-30P	NEMA	No
SRT5KXLT-IEC	5000	4800	Tower	208/240	208/240	3.5 (4800W)	10.7 (2400W)	No	L6-30P	IEC	No
SRT5KRMXLW-HW	5000	4500	3U	208/240, 230	208/240, 230	4.0 (4500W)	11.8 (2250W)	No	Hardwire Only	Hardwire Only	No
SRT5KXLI	5000	4500	Tower	230	230	4.0 (4500W)	11.8 (2250W)	No	Hardwire Only	IEC + Hardwire	No
Eaton®											
9PX5K	5000	4500	3U	208/240	208/240	3.0 (4500W)	10.0 (2250W)	No	Hardwire or L6-30P	NEMA + Hardwire	No
9PX5KTF5	5000	4500	6U	208/240	208/240 + 120	3.0 (4500W)	10.0 (2250W)	No	Hardwire or L6-30P	NEMA	No
9PX5KP1	5000	4500	6U	208/240	208/240 + 120	3.0 (4500W)	10.0 (2250W)	XFMR	Hardwire or L6-30P	NEMA	No
9PX5KP2	5000	4500	6U	208/240	208/240 + 120	3.0 (4500W)	10.0 (2250W)	XFMR	Hardwire Only	Hardwire Only	No
CyberPower®											
OL5KRTHD	5000	5000	2U	208/240	208/240	2.3 (5000W)	6.4 (2500W)	No	Hardwire or L6-30P	NEMA	1 Bank



Powering and Connecting Your World

See Next Page for 6kVA Models

# SMARTONLINE® UNITY PF UPS — MORE POWER IN LESS SPACE



- Add one or more smart external battery packs for extended runtime ([BP192V12RT3US](#) – 3U Rack BP)
- 4-post rack-mounting hardware included; 2-post rack-mounting hardware available\*
- Add [2-9USTAND](#) for tower
- Add [SU30ACORD](#) to convert hardwire-only input to L6-30P

\* Order [2POSTRMKITWM](#) for 3U models without "MB" suffix. Order [2POSTRMKITMB](#) for 3U models with "MB" suffix. Add an extra [2POSTRMKITWM](#) for all 5U models.

## 6kVA On-Line UPS Specifications: Tripp Lite vs. Competitors

Model	VA	Watts	Rack Size	Input Voltage	Output Voltage	Full-Load Runtime (min.)	Half-Load Runtime (min.)	Maint. Bypass	Included Input Options	Outlet Types	Outlet Control
Tripp Lite – All models feature unity (1.0) power factor, pure sine wave output, ENERGY STAR® 2.0, SNMP card, easy-access management console, temperature-compensated charging and front-panel LCD.											
<a href="#">SU6KRT3UHV</a>	6000	6000	3U	208/240	208/240	3.0 (6000W)	8.5 (3000W)	No	Hardwire or L6-30P	NEMA + Hardwire	3 Banks
<a href="#">SU6KRT3UHVMB</a>	6000	6000	3U	208/240	208/240	3.0 (6000W)	8.5 (3000W)	Yes	Hardwire or L6-30P	NEMA + Hardwire	3 Banks
<a href="#">SU6KRT3UTE</a>	6000	6000	5U	208/240	208/240 + 120	3.0 (6000W)	8.5 (3000W)	No	Hardwire or L6-30P	NEMA + Hardwire	3 Banks
<a href="#">SU6KRT3UTFMB</a>	6000	6000	5U	208/240	208/240 + 120	3.0 (6000W)	8.5 (3000W)	Yes	Hardwire or L6-30P	NEMA + Hardwire	3 Banks
<a href="#">SU6KRT3UG</a>	6000	6000	3U	200-240	200-240	3.0 (6000W)	8.5 (3000W)	No	Hardwire Only	IEC + Hardwire	3 Banks
<a href="#">SU6KRT3UGMB</a>	6000	6000	3U	200-240	200-240	3.0 (6000W)	8.5 (3000W)	Yes	Hardwire Only	IEC + Hardwire	3 Banks
<a href="#">SU6KRT3UHW</a>	6000	6000	3U	200-240	200-240	3.0 (6000W)	8.5 (3000W)	No	Hardwire Only	Hardwire Only	No
<a href="#">SU6KRT3UHWMB</a>	6000	6000	3U	200-240	200-240	3.0 (6000W)	8.5 (3000W)	Yes	Hardwire Only	Hardwire Only	No
<a href="#">SU6KRT3UX</a>	6000	6000	3U	220/230/240	220/230/240	3.0 (6000W)	8.5 (3000W)	No	Hardwire Only	IEC + Hardwire	3 Banks
<a href="#">SU6KRT3UXMB</a>	6000	6000	3U	220/230/240	220/230/240	3.0 (6000W)	8.5 (3000W)	Yes	Hardwire Only	IEC + Hardwire	3 Banks
APC®											
<a href="#">SRT6KRMXLT-IEC</a>	6000	6000	4U	208/240	208/240	2.3 (6000W)	8.3 (3000W)	No	Hardwire Only	IEC + Hardwire	No
<a href="#">SRT6KRMXLT-5KTF</a>	6000	6000	6U	208/240	208/240 + 120	2.3 (6000W)	8.3 (3000W)	No	Hardwire Only	NEMA + Hardwire	No
<a href="#">SRT6KXLT</a>	6000	6000	Tower	208/240	208/240	2.3 (6000W)	8.3 (3000W)	No	Hardwire Only	NEMA + Hardwire	No
<a href="#">SRT6KXLTUS</a>	6000	6000	Tower	208/240	208/240	2.3 (6000W)	8.3 (3000W)	No	Hardwire Only	NEMA + Hardwire	No
<a href="#">SRT6KXLT-IEC</a>	6000	6000	Tower	208/240	208/240	2.3 (6000W)	8.3 (3000W)	No	Hardwire Only	IEC + Hardwire	No
<a href="#">SRT6KXLT-5KTF</a>	6000	6000	Tower	208/240	208/240 + 120	2.3 (6000W)	8.3 (3000W)	No	Hardwire Only	NEMA + Hardwire	No
<a href="#">SRT6KRMXLI</a>	6000	6000	4U	230	230	2.5 (6000w)	8.7 (3000w)	No	Hardwire Only	IEC + Hardwire	No
<a href="#">SRT6KXLI</a>	6000	6000	Tower	230	230	2.5 (6000w)	8.7 (3000w)	No	Hardwire Only	IEC + Hardwire	No
Eaton®											
<a href="#">9PX6K</a>	6000	5400	3U	208/240	208/240	3.0 (5400W)	8.0 (2700W)	No	Hardwire or L6-30P	NEMA + Hardwire	No
<a href="#">9PX6KUS</a>	6000	5400	3U	208/240	208/240	3.0 (5400W)	8.0 (2700W)	No	Hardwire or L6-30P	NEMA + Hardwire	No
<a href="#">9PX6K-10</a>	6000	5400	3U	208/240	208/240	3.0 (5400W)	8.0 (2700W)	No	Hardwire or L6-30P	NEMA + Hardwire	No
<a href="#">9PX6KTF5</a>	6000	5400	6U	208/240	208/240 + 120	3.0 (5400W)	8.0 (2700W)	No	Hardwire or L6-30P	NEMA	No
<a href="#">9PX6KP1</a>	6000	5400	6U	208/240	208/240 + 120	3.0 (5400W)	8.0 (2700W)	XFMR	Hardwire or L6-30P	NEMA	No
<a href="#">9PX6KP2</a>	6000	5400	6U	208/240	208/240 + 120	3.0 (5400W)	8.0 (2700W)	XFMR	Hardwire or L6-30P	NEMA + Hardwire	No
CyberPower®											
<a href="#">OL6KRTHD</a>	6000	6000	2U	208/240	208/240	1.4 (6000W)	4.9 (3000W)	No	Hardwire or L6-30P	NEMA	1 Bank



Powering and Connecting Your World

[presaleshelp@tripplite.com](mailto:presaleshelp@tripplite.com)  
773.869.1773 | [tripplite.com](http://tripplite.com)