

Fibre Optical Cables

Multimode 50/125 OM3/OM4 Cable Indoor/Outdoor Loose Tube MPC with Rodent Protection

Anixter PN	Vendor PN	Description	Category
373-COR300GF-LTCT-04	004TEU-13188D2G	4F MM 50/125 OM3 CC FREEDM DRY MPC LT IN/OUT LSZH/FRNC 004TSZ-T2B80D20	OM3/OM4
373-COR300CC-LTCT-06	006TEU-13188A2G	6F MM 50/125 OM3 CLEARCURVE LT CT LSZH BLACK IN/OUT NON-MET/ LCXLM1-K0006-H700	OM3/OM4
373-COR300GF-LTCT-12	012TEU-13188D2G	12F MM 50/125 OM3 CC FREEDM DRY MPC LT IN/OUT LSZH/FRNC 012TSZ-T2B80D20	OM3/OM4
373-COR300CC-LTCT-24	024TEU-13188A2G	24F MM 50/125 OM3 CLEARCURVE L CT LSZH BLACK IN/OUT NON-MET/ LCXLM1-K0024-H700	OM3/OM4
373-COR550CC-LTCT-12	012TEU-13198A2G	12F MM50/125 OM4 CLEARCURVE L CT LSZH BLACK IN/OUT NON-MET/ LCXLM1-K0012-K700	OM3/OM4
373-COR550CC-LTCT-24	024TEU-13198A2G	24F MM 50/125 OM4 IN/OUT LOOSE ALL DIEL LSZH/FRNC NON MET ROD LCXLM1-K0024-K700	OM3/OM4
373-COR550-LTD-24E	024TRU-T3198A2G	24F (2X12)MM 50/125 OM4 IN/OUT LT LSZH/FRNC BLACK NON-MET LCXLM1-K4024-K700	OM3/OM4

Multimode 50/125 OM3/OM4 Cable Indoor/Outdoor Tight Buffer without Rodent Protection

Anixter PN	Vendor PN	Description	Category
373-COR300-TBDNP-06	006T8X-32188E2G	6F MM 50/125 OM3 I-MUC TB CC IN/OUT 900UM LSZH/FRNC LCXLN2-L5006-H700	OM3/OM4
373-COR300-TBDNP-12	012T8X-32188E2G	12F MM 50/125 OM3 I-MUC TB CC IN/OUT 900UM LSZH/FRNC LCXLN2-L5012-H700	OM3/OM4

373-COR300-TBDNP-24	024T8X-32188E2G	24F MM 50/125 OM3 I-MUC TB CC IN/OUT 900UM LSZH/FRNC LCXLN2-L5024-H700	OM3/OM4
---------------------	-----------------	---	---------

Multimode 50/125 OM3/OM4 Cable Indoor Tight Buffer i-MIC

Anixter PN	Vendor PN	Description	Category
374-COR300CC-TBD-04	004T8Z-32188E2G	4F MM 50/125 OM3 CLEARCURVE TB I-MIC INDOOR LSZH/FRNC AQUA LCXLI2-L5004-H700	OM3/OM4
374-COR300CC-TBD-06	006T8Z-32188E2G	6F MM 50/125 OM3 CLEARCURVE TB I-MIC INDOOR LSZH/FRNC AQUA LCXLI2-L5006-H700	OM3/OM4
374-COR300CC-TBD-12	012T8Z-32188E2G	12F MM 50/125 OM3 CLEARCURVE T I-MIC INDOOR LSZH/FRNC AQUA LCXLI2-L5012-H700	OM3/OM4
374-COR300CC-TBD-24	024T8Z-32188E2G	24F MM 50/125 OM3 CLEARCURVE T I-MIC INDOOR LSZH/FRNC AQUA LCXLI2L5024H700	OM3/OM4
374-COR550CC-TBD-06	006T8Z-32198E2G	6F MM 50/125 OM4 CLEARCURVE TB I-MIC INDOOR LSZH/FRNC AQUA LCXLI2-L5006-K700	OM3/OM4
374-COR550CC-TBD-12	012T8Z-32198E2G	12F MM 50/125 OM4 CLEARCURVE TB 900UM I-MIC IN LSZH/FRNC LCXLI2-L5012-K700	OM3/OM4
374-COR550CC-TBD-24	024T8Z-32198E2G	24F MM 50/125 OM4 CLEARCURVE T I-MIC INDOOR LSZH/FRNC AQUA LCXLI2-L5024-K700	OM3/OM4