



## ANGLE BUSBAR COVER (BCIC)

### WILDLIFE AND ASSET PROTECTION PRODUCTS

#### KEY FEATURES

- Modular/Wraparound product design
- Retrofit insulation on 3-4 inch angle busbars
- Suitable for indoor and outdoor use
- Quick and easy to install

TE Connectivity's (TE) BCIC Angle Busbar covers provide high quality electrical insulation for substation support bus work. These covers are made from a non-tracking BCIC material that is suitable for harsh medium voltage outdoor environments.

BCIC Angle Busbar covers are split for easy installation and removal. Its modular, wraparound design provides quick and simple installation. Overlapped sections together, produce increased busbar coverage.

The BCIC Angle Busbar cover will provide flashover protection up to 35 kV. The Angle Bus Covers provide insulation when existing equipment can not be dismantled.

**Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.**

## Angle Bus Cover (BCIC)



TE's wildlife and asset protection products and systems of tubes, tapes, sheets, pre-formed covers and barriers provide a proven, cost-effective and easy-to-install solution to bird, animal and weather related outages.

### PRODUCT SELECTION INFORMATION

Description	Color	Recommended Bus Bar	Supplied Length	Standard Pack
BCIC-ANGLE-4X48(B6)	Red	3" - 4" (75mm - 100mm)	4ft	6 pieces
BCIC-G-ANGLE-4X48(B6)	Gray	3" - 4" (75mm - 100mm)	4ft	6 pieces

### TECHNICAL REPORT

EDR-5594: Electrical testing of BCIC-Angle Bus Cover

[te.com/energy](http://te.com/energy)

©2014, 2016 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2730-DDS-5/16-EN-AMS-BCIC-Angle-Raychem E557

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

### FOR MORE INFORMATION:

#### TE Technical Support Centers

USA: + 1 800 327 6996  
France: + 33 380 583 200  
UK: + 44 0870 870 7500  
Germany: + 49 896 089 903  
Spain: + 34 916 630 400  
Italy: + 39 333 250 0915  
Benelux: + 32 16 351 731  
Canada: + 1 (905) 475-6222  
Mexico: + 52 (0) 55-1106-0800  
Latin/S. America: + 54 (0) 11-4733-2200  
China: + 86 (0) 400-820-6015