



## Blowing Equipment and Accessories



BE200



BEPT001



BE2MFT (red) and BE3MFT (black)



BEREG02

### Description:

Sumitomo Electric Lightwave's cable blowing head is used to blow the compact fiber optic bundles through the tube cable on a stream of air or nitrogen gas. Installation is completely stress-free, eliminating the damage that can occur when traditional fiber is pulled through the network.

### Features

- System consists of a payoff stand on which reels of fiber bundles are placed; a blowing head used to direct the fiber bundles; a pressure regulator and air source
- Air source is either compressed air or bottles of compressed nitrogen
- Pressure regulator with 0-200 psi output pressure
- Fiber bundles are blown at rates up to 150 feet per minute. Speed is controlled by air flow rate through motor

### Ordering Information

Part Number	Description
BE200RM	Blowing Head Kit, Monthly Rental
BE200RS	Blowing Head Kit, Semi-annual Rental
BE200RY	Blowing Head Kit, Yearly Rental
BE200LRM	Blowing Head Kit, Monthly Rental (Long Reel for 72-Fiber Bundle and/or Fiber Bundle Extended Length)
BE200LRS	Blowing Head Kit, Semi-annual Rental (Long Reel for 72-Fiber Bundle and/or Fiber Bundle Extended Length)
BE200LRY	Blowing Head Kit, Yearly Rental (Long Reel for 72-Fiber Bundle and/or Fiber Bundle Extended Length)
BE02DW	Blowing Head Drive Wheels 2, 4 or 6 and 12-Fiber Single Sub-unit Bundle / Red
BE02SL	Blowing Head Seal 2, 4 or 6 and 12-Fiber Single Sub-unit Bundle / Black
BE03DW	Blowing Head Drive Wheels (12 Legacy, 18, 24, 48 or 72-Fiber Bundle) / Black
BE03SL	Blowing Head Seal (12 Legacy, 18 or 24-Fiber Bundle) Black
BE04SL	Blowing Head Seal (48 and 72-Fiber Bundle) Black
BE08CTB	BB Catcher with 8mm Fittings
BE2MFT	Reusable, threaded, aluminum tip for installing 2, 4 or 6 and 12-Fiber Single Sub-unit Bundle
BE3MFT	Reusable, threaded, aluminum tip for installing 12 Legacy to 72-fiber bundles
BEPT001	Tube Testing Kit, for Pressure & Obstruction Tests
BEPT0S	Pressure Test Switch
BEBB01P	5 mm Plastic Beads (for Obstruction Testing)
BEPTGA	Test Gauge - Handheld Pressure Gauge with 8mm Fitting for Tube Pressure Testing
BEBB40P	4 mm Plastic Beads (for Obstruction Testing of TCxxTP2 series)
BEREG02	Single Stage Nitrogen Tank Regulator, 0-200 psi
BEISOV1	Dual-Tank Isolation Valve Kit - for using 2 nitrogen bottles
BEREGCA	Regulator adapter for compressed air cylinders
BETC001	Tube Cutter
BETC00B	Replacement Blade for Tube Cutter
BETLLO3	Tube Cable Cutter (Replaced BETL01 and BETL02)

\* Blowing head kits are leased only to Sumitomo Electric Lightwave licensed installers.