



ZEUS Series Commercial & Industrial Surge Protective Devices



DITEK's ZEUS Series Surge Protective Devices (SPDs) are designed to provide the professional-grade electrical protection that facility managers need, backed by a limited 10-year warranty. Each model incorporates the latest in surge protection technology for maximum performance and protection, while providing high surge current ratings to ensure long service life. Many models incorporate additional assurance features that help alert building management of their current status so that managers can take action to maintain continued protection. Units are available in a wide range of voltage configuration and protection modes to meet all of your project specification needs.



Surge Protection for EVERY Application



D200M / D300M Series Modular Surge Protective Devices

- UL1449 4th Edition Listed, Type 1 SPD
- 200kA or 300kA per phase Surge Current Rating
- NEMA 4 Enclosure
- Field Replaceable Surge Protection Module
- Surge Counter, Audible Alarm, Advanced Diagnostic LEDs per phase
- Dry Contacts for Remote Notification of Surge Protection Status
- Listed in MasterSpec®

Find us in

MasterSpec®

a product of The American Institute of Architects

D200M/300M-120/2401	120/240 VAC, Split-Phase, 3 Wire + Ground
D200M/300M-120/2083Y	120/208 VAC, 3-Phas Wye, 4 Wire + Ground
D200M/300M-277/4803Y	277/480 VAC, 3-Phase Wye, 4 Wire + Ground
D200M/300M-2403D	240 VAC, 3-Phase Delta, 3 Wire + Ground
D200M/300M-4803D	480 VAC, 3-Phase Delta, 3 Wire + Ground



D200MT / D300MT Series Modular Surge Protective Devices w/Integral Disconnect

- UL1449 4th Edition Listed, Type 1 SPD
- 200kA or 300kA per phase Surge Current Rating
- NEMA 4 Enclosure, UL98 Integral Disconnect Switch
- Field Replaceable Surge Protection Module
- Surge Counter, Audible Alarm, Advanced Diagnostic LEDs per phase
- Dry Contacts for Remote Notification of Surge Protection Status
- Listed in MasterSpec®

Find us in

MasterSpec®

a product of The American Institute of Architects

D200M/300M-120/2401T	120/240 VAC, Split-Phase, 3 Wire + Ground
D200M/300M-120/2083YT	120/208 VAC, 3-Phas Wye, 4 Wire + Ground
D200M/300M-277/4803YT	277/480 VAC, 3-Phase Wye, 4 Wire + Ground
D200M/300M-2403DT	240 VAC, 3-Phase Delta, 3 Wire + Ground
D200M/300M-4803DT	480 VAC, 3-Phase Delta, 3 Wire + Ground



D50 / D100 / D200 Series Non-Modular Surge Protective Devices

- UL 1449 4th Edition Listed, Type 1 SPD with NEMA 4X Enclosure
- 50kA, 100kA or 200kA per phase Surge Current Rating
- D200 Series includes Audible Alarm with Switch & Dry Contacts for Remote Monitoring

D50/100/200-120/2401	120/240 VAC, Split-Phase, 3 Wire + Ground
D50/100/200-120/2083Y	120/208 VAC, 3-Phas Wye, 4 Wire + Ground
D50/100/200-120/240HL	120/240 VAC, 3-Phase Delta High Leg
D50/100/200-277/4803Y	277/480 VAC, 3-Phase Wye, 4 Wire + Ground
D50/200-347/6003Y	347/600 VAC, 3-Phase Wye, 4 Wire + Ground
D50-2401	240 VAC, Single Phase, 2 Wire + Ground
D50/100/200-2403D	240 VAC, 3-Phase Delta, 3 Wire + Ground
D50/100/200-4803D	480 VAC, 3-Phase Delta, 3 Wire + Ground
D100-6003D	600 VAC, 3-Phase Delta, 3 Wire + Ground

DITEK Corporation



DITEK is the gold standard in quality surge protection, networking solutions and UPS systems for the commercial and industrial market. We provide solutions for Networking and Video Surveillance, Fire, Intrusion, Access Control, AC Power and Data/Signaling applications.

At DITEK's ISO 9001 certified manufacturing facility in Largo, FL; a highly-trained and culturally diverse workforce utilizes state-of-the-art equipment and lean manufacturing methodologies. DITEK's Technical Support Team is available to answer application or installation questions by phone or internet live chat. Live and web-based product training, CEU courses and collateral materials are readily available through our Marketing Services Group.



Technical Support: 888-472-6100

800-753-2345

www.diteknetworks.com



One DITEK Center
1720 Starkey Road
Largo, FL 33771

Document: SMS-100028-001 (920-010) Rev 9/06/21