

VM17LED 17" LED monitor
VM19LED 19" LED monitor



**ECO-FRIENDLY - LOW ENERGY CONSUMPTION
GREENER THAN LCDs**

Features

- Displays up to 16.7 million colors
- 1280(H) x 1024(V) SXGA resolution
- Built-in speakers
- Convenient front controls for screen programming
- Input signal detection provides easy connection
- 290cd/m2 Brightness
- 500:1 Contrast ratio
- HDMI, VGA (D-Sub 15 pins), audio, video inputs
- Regulated 12VDC 40W (UL & CSA listed power supply included)
- VESA compatible
- 2 year warranty

Specifications

Monitor	VM17LED	VM19LED
Composite Output	BNC x 2	
Composite Input	BNC x 2	
Single Connector	VGA x 1, RCA x 2, PC Audio x 1, HDMI x 1	
Speaker	1.5W x 2	
Display Mode	Video 1 / Video 2 / PC / HDMI	
AC Power	AC 100 - 240V 50/60Hz	
Temperature	Operation: 32° F - 104° F / Storage: 14° F - 140° F	
Power Consumption	15W Max. in "ON" mode Under 3W in power saving mode (100 VAC), Under 5W in power saving mode (240 VAC)	
OSD Control	Picture Mode, Contrast, Brightness, Color, Tint, Sharpness, Color Temp., DNR	
OSD Languages	English, German, French, Italian, Spanish, Russian, Turkish, Polish, Dutch, Czech	
Auto Adjustment	Yes (Only for VGA mode)	
De-interlace	Yes	
Wall Mount	Optional	
Accessories	Adapter, power cord, manual VGA cable	
Safety	UL, FCC, CE, RoHS	
Tilt	5°-15°	
Humidity	10% - 90%	
Monitor Scan	Microprocessor controlled	
Pixel Pitch	0.264 x 0.264mm	0.294 - 0.294mm
Pixel Format	1280 x 1024	1280 x 1024
Response Time	5ms	5ms
Color Depth	16.7 Million colors	
Viewing Angle	Vertical -80°, 80° / Horizontal -85°, 85°	
Display Area	13.3" H x 10.6" V	14.8" H x 11.8" V
Dimensions	15.1" W x 15.1" H x 6.4" D	16.7" W x 16.3" H x 6.5" D
Weight	7.5 lbs.	7.7 lbs.

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 1/25/12

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880

www.specotech.com