

## Better Quality. Better Prices.

### Features

- TAA Compliant
- Hot-Pluggable SFP Footprint
- Compliant with SFP Multi-Sourcing Agreement (MSA)
- Digital Diagnostic Monitoring (DMI) (on some modules)

### Benefits

- Utilize Existing Equipment
- Pay as You Grow Strategy to Accomodate Network Growth
- Multimode and Single Mode Fiber Solutions
- Extended Operating Temperatures (on some modules)

### Specifications

Standards	IEEE 802.3
Power Input	3.3V
Environment	Operating: 0°C to +70°C Operating: -40°C to +85°C (Some Extended Temperature Modules)
Compliance	IEC60825, FDA 21, CFR 1040.10 and 1040.11
Warranty	Lifetime



+1.952.941.7600 | [www.transition.com](http://www.transition.com) | [sales@transition.com](mailto:sales@transition.com)

*\* New pricing valid for select Cisco Compatible SFPs. Save 14-83% off; see individual products for details.*

# Cisco Compatible SFPs

Anixter Part	Transition Networks Part	Description
<b>Fast Ethernet</b>		
392708	TN-GLC-FE-100FX	100Base-FX multimode (LC) [2 km / 1.2 mi.]
<b>Duplex Gigabit Ethernet</b>		
379193	TN-GLC-SX-MM	1000Base-SX 850nm multimode (LC) [62.5/125 μm: 220 m/722 ft.] [50/125 μm: 550 m/1804 ft.]
600977	TN-GLC-SX-MMD	1000Base-SX 850nm multimode (LC) with DMI [6.25/125 μm: 220m/722ft.] [50/125μm: 550m/1804 ft.]
392707	TN-GLC-SX-MM-2K	1000Base-SX 1300nm Ext. multimode (LC) [2 km/1.2 mi.]
546034	TN-GLC-SX-MM-RGD	1000Base-SX 850nm multimode (LC) with DMI [62.5/125 μm: 220 m/722 ft.] [50/125 μm: 550 m/1804 ft.] -40°C to +85°C
423412	TN-SFP-GE-S	1000Base-SX 850nm multimode (LC) with DMI [62.5/125 μm: 220 m/722 ft.] [50/125 μm: 550 m/1804 ft.] -40°C to +85°C
423413	TN-SFP-GE-L	1000Base-LX 1310nm single mode (LC) with DMI [10 km/6.2 mi.] -40°C to +85°C
379228	TN-GLC-LH-SM	1000Base-LX 1310nm single mode (LC) [10 km/6.2 mi.]
570646	TN-GLC-LH-SMD	1000Base-LX 1310nm single mode (LC) with DMI [10km/6.2 mi.]
556125	TN-GLC-LX-SM-RGD	1000Base-LX 1310nm single mode (LC) with DMI [10 km/6.2 mi.] -40°C to +85°C
<b>Simplex Gigabit Ethernet</b>		
392701	TN-GLC-BX-U	1000Base-BX 1310nm TX/1490nm RX single fiber single mode (LC) with DMI [10 km/6.2 mi.]
392702	TN-GLC-BX-D	1000Base-BX 1490nm TX/1310nm RX single fiber single mode (LC) with DMI [10 km/6.2 mi.]
600976	TN-GLC-BX-U-20	1000Base-BX 1310nm TX/1490nm RX single fiber single mode (LC) with DMI [20 km/12.4 mi.]
600975	TN-GLC-BX-D-20	1000Base-BX 1490nm TX/1310nm RX single fiber single mode (LC) with DMI [20 km/12.4 mi.]
<b>Copper Gigabit Ethernet</b>		
379192	TN-GLC-T	1000Base-T (RJ-45) [100 m/328 ft.]
<b>10 Gigabit Ethernet</b>		
487174	TN-SFP-10G-SR	10GBase-SR, SFP+ with DMI 850nm multimode (LC) [300/82/33 m; 985/269/108 ft.]
487179	TN-SFP-10G-LR	10GBase-LR, SFP+ with DMI 1310nm single mode (LC) [10 km/6.2 mi.]
987238	TN-SFP-10G-LR-PK	Pack of (20) TN-SFP-10G-LR: 10GBase-LR, SFP+ with DMI 1310nm single mode (LC) [10 km/6.2 mi.]
487181	TN-SFP-10G-ER	10GBase-ER, SFP+ with DMI 1550nm single mode (LC) [40 km/24.9 mi.]
<b>40 Gigabit Ethernet</b>		
987234	TN-QSFP-40G-LR4	40GBase-LR4, 1271nm, 1291nm, 1311nm, 1331nm, single mode (LC) [10km/6.2mi.] with DMI