

READY!SM GRIP LOW-PROFILE MEDIUM-VOLTAGE PULLING EYES

Reduce Cable Waste and Labor Costs with Single-Use Pulling Eyes

Anixter's single-use pulling eye system for medium-voltage cable is a cost-effective alternative to traditional pulling eyes. Installed by Anixter prior to shipment, these eyes reduce cable waste and labor costs. The eyes are installed using sealant to make them block moisture during the pull. They also come with staggered lanyards for easy installation in conduit.

Features

- Water-barrier with sealant and heat-shrink tubing
- Installed in clean, protected environment
- Staggered lanyards
- Shipped with cold-shrink end caps

NOTE: For installations where the cable ends may be submerged for a long period of time, the pulling eye should be cut off after the pull and the cold shrink end cap should be applied.

Benefits

- Reduces on-site labor for installing eyes
- Reduces material to order, receive and unpack
- Reduces the need for tooling
- Provides more security than grips
- Eliminates messy residue
- Leaves less conductor scrap
- Makes pulling in conduit easier
- Reduces injury from on-site installation
- Prevents long-term moisture with end caps

8 KV SHIELDED OR UNSHIELDED			SEALANT KIT + PULLING EYE = MEDIUM VOLTAGE PULLING EYE							
GAUGE	JACKET OD	ICEA MAX LOAD PULLING TENSION (LBS)	ANIXTER PN SEALANT KIT	PULLING EYE WITH LANYARD						
				11 INCH	14 INCH	15 INCH	19 INCH	21 INCH	28 INCH	35 INCH
2	0.78	530	MVKit-1.10-0.35-EC2	452033		452034	452035			
1/0	0.91	845	MVKit-1.10-0.35-EC2		452049			452050	452051	452052
2/0	0.96	1,065	MVKit-1.10-0.35-EC2		453459			453460	453461	453462
4/0	1.05	1,690	MVKit-1.50-0.47-EC2		452053			452054	452055	452056
250MCM	1.11	2,000	MVKit-1.50-0.47-EC3		452057			452058	452059	452060
350MCM	1.21	2,800	MVKit-1.50-0.47-EC3		461747			461748	461749	461750
500MCM	1.36	4,000	MVKit-1.50-0.47-EC3		452061			452062	452063	452064
15KV SHIELDED										
GAUGE	JACKET OD	ICEA MAX LOAD PULLING TENSION (LBS)	ANIXTER PN SEALANT KIT	PULLING EYE WITH LANYARD						
				11 INCH	14 INCH	15 INCH	19 INCH	21 INCH	28 INCH	35 INCH
2	1.04	530	MVKit-1.10-0.35-EC2	452033		452034	452035			
1/0	1.13	845	MVKit-1.50-0.47-EC3		452049			452050	452051	452052
2/0	1.16	1,065	MVKit-1.50-0.47-EC3		453459			453460	453461	453462
4/0	1.29	1,690	MVKit-1.50-0.47-EC3		452053			452054	452055	452056
250MCM	1.34	2,000	MVKit-1.50-0.47-EC3		452057			452058	452059	452060
350MCM	1.44	2,800	MVKit-1.50-0.47-EC3		461747			461748	461749	461750
500MCM	1.57	4,000	MVKit-2.00-0.63-EC3		452061			452062	452063	452064


Corporate Snapshot



The Anixter Difference

At Anixter, we help build, connect, power and protect valuable assets and critical infrastructures. From enterprise networks to industrial support and supplies to video surveillance applications and electric power transmission and distribution, we offer full-line solutions—and intelligence—that create reliable, resilient systems that can sustain your business and community. Through our unmatched global distribution network, supply chain management expertise and technical know-how, we drive efficiency and effectiveness to benefit your bottom line.

Corporate Snapshot



Global Reach. Local Advantage.

With Anixter, you get a true local partner around the world. No other distributor of our kind can claim an in-country presence in approximately 50 countries and in over 300 cities.

We do business in more than 35 currencies and 30 languages, which means we are uniquely positioned to help facilitate your project in the local environment, reduce risks and keep costs down.

About Anixter: anixter.com/aboutus
Legal Statement: anixter.com/legalstatement

Anixter Inc. World Headquarters
 2301 Patriot Boulevard
 Glenview, Illinois 60026
 224.521.8000

16D6845GL © 2018 Anixter Inc. 1/18

1.800.ANIXTER | anixter.com



Products. Technology. Services. Delivered Globally.