


PRODUCT SOLUTIONS BRIEF  
**RARITAN**

**HEALTHCARE FACILITY POWER OPTIMIZATION**



Through our strong global partnerships and alliances with manufacturers such as Raritan, we are able to present you with the following offering to meet your specific healthcare facility requirements.

**PX iPDU**

Raritan's PX iPDU series offers real-time remote power monitoring of current amps, voltage, power kVA, kW and energy consumption kWh with +/- 1 percent billing-grade accuracy. There are hundreds of models available to meet all of your data center applications including outlet-level metering and switching and 400 V three-phase power distribution.

**CHALLENGE SOLVERS**

- Colored chassis are available in 10 colors that help reduce errors and make it easier to identify power feeds and perform troubleshooting to minimize downtime.
- Models that feature energy-efficient latching relays consume 67 percent less energy than nonlatching models and can be configured to return to pre-outage phase instantly.
- Accurate kWh metering allows you to measure actual energy usage for customer or department charge-back, establishing baselines and analyzing the effect of initiatives.
- Support for plug-and-play environment sensors allow you to monitor temperature, humidity, airflow and other environmental conditions.

**THE ANIXTER APPROACH**

- **Facility Power**  
Design scalable solutions that cater to healthcare growth and flexibility.
- **Conditioned Power**  
Maintain continuous voltage and protect against surges with conditioning technology.
- **Backup Power**  
Provide optimal settings for quality patient care with an always-on environment.

- **Efficient Power**  
Consider highly efficient solutions that maximize power quality and minimize operational expenses.
- **Monitored Power**  
Adopt an integrated power solution that can be metered, monitored and designed for continuity.

**THE RARITAN SOLUTION**

PDU TYPE	MONITORING CAPABILITY	ACCESSORY OPTIONS
Metered Switched	Inlet Outlet	Software Sensors Locking cords

[anixter.com/shopraritan](http://anixter.com/shopraritan)




Available in 10 colors that help reduce human error by making it easier to identify power feeds


**Raritan**  
 A brand of **legrand**

**WHAT WE HEAR**

Healthcare stakeholders are dealing with a variety of challenges:



Meeting **ENERGY EFFICIENT** goals



**PREVENTING** accidental outages



Ensuring an **ALWAYS ON** environment



Reducing **UTILITY COSTS**



Restrictions of **LEGACY ELECTRICAL INFRASTRUCTURE**

**Infrastructure as a Platform**  
 by Anixter

Infrastructure as a Platform by Anixter provides a practical, configurable and integrated approach to retrofitting or building a critical power chain in your healthcare environment.

## CONFIGURE

We help you discover and map your specific needs to the best solution.

- Input voltage and current
- Input plug type
- Outlet quantity and type
- Unit or outlet level metering

## BUNDLE

Your validated, preconfigured solutions are packaged and site ready.

- Cabinet and racks
- Power IQ® monitoring software
- Environmental sensors
- SecureLock™ power cords

## DEPLOY

Controlled, repeatable solutions are delivered on time and under budget.

- Custom packaging and labeling
- Time-sensitive delivery options
- Staged project shipping
- Tailored last-mile delivery

## RARITAN SMART-UPS ONLINE FEATURES

### ✓ PREVENT AND MITIGATE OUTAGES

- 60°C (140°F) max temp
- Alternate-phase sequenced outlets
- User-configurable power on sequencing
- Remote power control
- Available in 10 colors to help identify power feeds
- Intelligent replaceable controller
- Turns outlets off to prevent unauthorized power usage

### ✓ MONITOR POWER CAPACITY

- Outlet switching for remote power control
- Inlet, outlet and branch circuit level metering
- Local and remote Web-based monitoring and alarms
- Seamlessly integrates with Power IQ
- +/- 1 percent kWh metering accuracy
- Brilliant on-board color display



Intelligent replaceable controller with hot-swap capability reduces downtime.

**FOR MORE DETAILS VISIT [ANIXTER.COM/SHOPRARITAN](https://www.anixter.com/shopraritan)**